



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



71A5692001D 200W Pulse Start MH Multi Tap M136

Advance By Signify

Catalog Number	71A5692001D
Manufacturer	Advance By Signify
Description	Reliable Performance Vacuum-Pressure Impregnation Is Used to Re-Enforce The Electrical Insulation Of The Ballast, Preclude Moisture, Inhibit Noise, and Dissipate Heat;Pre-Insulated Voltage Leads Reduce The Risk Of Shock and Shrink Installation Time The Basic Ballast Is The Open Core and Coil Which Is Most Often Used As A Component Within A Lighting Luminaire. The Core and Coil Also Forms The Nucleus Of Philips Advance'S Five Other Ballast Configurations. Vacuum-Pressure Impregnated With A Silica-Filled Pol
Weight per unit	8.6 (lbs/each)
Product Category	Hid Ballast Kits

Features

ANSI Code	M136
Ballast Factor	1
dimnable	No
Lamp Type	METAL HALIDE
Number of Lamps	1
Power Factor	0.90
Power Rating	200
start type	Pulse
Voltage Rating	120/208/240/277
Wattage	200

Dimensions and Weight

Height	1.42
Length	15.55
Width	1.1



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	200W PULSE START MH MULTI TAP M136
extra long description	ADV 193060 MH BAL 200W M136 QUAD KI
Long Description	Reliable performance Vacuum-pressure impregnation is used to re-enforce the electrical insulation of the ballast, preclude moisture, inhibit noise, and dissipate heat;Pre-insulated voltage leads reduce the risk of shock and shrink installation time The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations. Vacuum-pressure impregnated with a silica-filled pol
Product Type	MH Bal 200W M136 Quad Kit
Special Features	Suitable for Outdoor; UL Listed, CSA, RoHS

Manufacturer Information

Brand	Signify Electronics
GTIN	00781087093474
Manufacturers Part Number	193060
UPC	781087093474

Taxonomies, Classifications, and Categories

Category Description	HID BALLASTS
Type	Magnetic HID

Packaging

Carton	1
Weight	8.56
Weight Per each	8.56

Uses, Certifications, and Standards

Application	Lighting Luminaire Component
Frequency Rating	60
standard	ULR;CSA certificate;RoHS Compliant