



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **72C5581NP001 1-175W 120/277 Bal** *Advance By Signify*

Catalog Number	72C5581NP001
Manufacturer	Advance By Signify
Description	Versatility In Commercial Applications Low Noise For Indoor Use;Two Dual Voltage Configurations Available: 120V/277V For The U.S Market and 120V/347V For The Canadian Market The Philips Advance Line Of F-Can Hid Ballasts Comes In Two Dual-Voltage Configurations For The Us and Canadian Market. Ballasts For These Luminaires Are Most Often Encased and Potted In Fluorescent Ballast Type Cans. Utilizes UI Class A (90°C) Insulation;Has Built-In, Automatically Resetting, Thermal Protector Which Disconnects The Ba
Weight per unit	11.3 (lbs/each)
Product Category	Pulse Start Hid Ballasts

### **Features**

amperage rating	0.85/0.36
ANSI Code	M57/107
Ballast Factor	1
Circuit Type	CWA
Lamp Type	METAL HALIDE
Number of Lamps	1
Power Factor	0.90
Power Rating	175/150
start type	Probe
Voltage Rating	120/277
Wattage	175
Wire Length	12
Wire Type	STRANDED

### **Material, Color, and Finish**

Housing Material	Metal
------------------	-------

### **Dimensions and Weight**

Height	1.02
Length	0.47
Width	1.54



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	1-175W 120/277 BAL
extra long description	ADV 494245 MH BAL 175W M57 120/277V
Long Description	Versatility in commercial applications Low noise for indoor use;Two dual voltage configurations available: 120V/277V for the U.S market and 120V/347V for the Canadian market The Philips Advance line of F-can HID ballasts comes in two dual-voltage configurations for the US and Canadian market. Ballasts for these luminaires are most often encased and potted in fluorescent ballast type cans. Utilizes UL Class A (90°C) insulation;Has built-in, automatically resetting, thermal protector which disconnects the ba
Product Type	MH Bal 175W M57 120/277V Fcan
Special Features	Suitable for Outdoor; UL, CSA, RoHS

## Manufacturer Information

Brand	Signify Electronics
GTIN	00781087025307
Manufacturers Part Number	494245
UPC	781087025307

## Taxonomies, Classifications, and Categories

Category Description	HID BALLASTS
Type	Magnetic HID

## Packaging

Carton	1
Weight Per each	11.34

## Uses, Certifications, and Standards

Frequency Rating	60
standard	CSA certificate;UL certificate;RoHS Compliant