



Catalog Number: 8104-SC1-NK  
Item Description: N1 SCREW COVER ENCL NK  
UPC Code: 784572108806



Brand Name: Milbank  
Type: Screw Cover  
Special Features: Cover Secured with Plated Screws  
Application: Enclosure for Mounting Electrical Equipment  
Standard: UL Listed  
Number Of Outlet: 0  
Material: Steel with Powder Coat Finish  
Color: ANSI 61 Gray  
Mounting: Wall Mount  
NEMA Rating: Type 1




*Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.*

CATALOG#	LABEL#
8104-SC1-( )	1002135
RC-8104-SC1-( )	1125021
SPSC-1084( )	1132714

NO.	CRS/QTY.	PART NO	DESCRIPTION
1	1	1010827	BACK WELDMENT
2	1	1002475	BAG ASSY, GROUND SCREW (NOT SHOWN)
3	1	1002646	BAG ASSY, SCREWS (NOT SHOWN)
4	1	1011627	CARTON
5	1	(SEE CHART)	COVER PLATE
6	1	(SEE CHART)	LABEL, UL LISTING





1 5 6 (APPLY INSIDE BACK)



CATALOG P/N	ROI P/N	MATERIAL	FINISH
8104-SC1	1011771	CRS	ANSI 61 GRAY
8104-SC1-NP	1104173	GALVANIZED	NO PAINT

REV.	DATE	DESCRIPTION	ECO No.	BY
*3	8/26/15	FIXED CATALOG CONFIGURATION, CHANGED MLB CARTON # TO MATCH PRINT CARTON #	032721	BNM

Material:	SEE CHART	 <p>KANSAS CITY, MO USA</p>
Shear/Die No.:		
Finish:	SEE CHART	
Part Wt.:	LBS. EA.	
Paint Qty.:	GRAMS	Title: 8 x 10 x 4 SCREW COVER TYPE 1 ENCLOSURE
Tolerances:	Third Angle	Catalog No.:
Unless Specified Otherwise		SEE CHART
X.X ±.1		Customer:
X.XX ±.03		MILBANK STD.
X.XXX ±.015		Drawing No.:
X" ±2"		1011771
Scale: NTS	Checked By:	Date:
Drawn By:	Approved By:	Sheet: 1 of 1



Catalog Number: 8104-SC1-NK  
Item Description: N1 SCREW COVER ENCL NK  
UPC Code: 784572108806



Brand Name: Milbank  
Type: Screw Cover  
Special Features: Cover Secured with Plated Screws  
Application: Enclosure for Mounting Electrical Equipment  
Standard: UL Listed  
Number Of Outlet: 0  
Material: Steel with Powder Coat Finish  
Color: ANSI 61 Gray  
Mounting: Wall Mount  
NEMA Rating: Type 1




*Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.*

CATALOG#	LABEL#
8104-SC1-( )	1002135
RC-8104-SC1-( )	1125021
SPSC-1084( )	1132714

NO.	CRS/QTY.	PART NO	DESCRIPTION
1	1	1010827	BACK WELDMENT
2	1	1002475	BAG ASSY, GROUND SCREW (NOT SHOWN)
3	1	1002646	BAG ASSY, SCREWS (NOT SHOWN)
4	1	1011627	CARTON
5	1	(SEE CHART)	COVER PLATE
6	1	(SEE CHART)	LABEL, UL LISTING



1 5 6 (APPLY INSIDE BACK)



CATALOG P/N	ROI P/N	MATERIAL	FINISH
8104-SC1	1011771	CRS	ANSI 61 GRAY
8104-SC1-NP	1104173	GALVANIZED	NO PAINT

REV.	DATE	DESCRIPTION	ECO No.	BY	Material:	SEE CHART	Shear/Die No.:	Finish:	SEE CHART	Part Wt.:	LBS. EA.	Paint Qty.:	GRAMS	Title:	8 x 10 x 4 SCREW COVER TYPE 1 ENCLOSURE	Catalog No.:	SEE CHART	Customer:	MILBANK STD.	Drawing No.:	1011771
*3	8/26/15	FIXED CATALOG CONFIGURATION, CHANGED MLB CARTON # TO MATCH PRINT CARTON #	032721	BNM	Material:	SEE CHART	Shear/Die No.:	Finish:	SEE CHART	Part Wt.:	LBS. EA.	Paint Qty.:	GRAMS	Title:	8 x 10 x 4 SCREW COVER TYPE 1 ENCLOSURE	Catalog No.:	SEE CHART	Customer:	MILBANK STD.	Drawing No.:	1011771
					Scale:	NTS	Checked By:			Approved By:			Date:			Sheet:	1 of 1				

