



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



870BKG Radiant Switch 1P 15A 120/277V BK

Pass & Seymour/Legrand

| | |
|------------------|---|
| Catalog Number | 870BKG |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Decorator SWITCH1POLE 15AMP 120/277V Grounding, Black |
| Weight per unit | 0.1400 (lbs/each) |
| Product Category | Gen Purpose Switches |

Features

| | |
|--------------------|---------------|
| gang | 1 |
| insulation | Bare |
| Material | Thermoplastic |
| media | Yes |
| Mounting Type | Box |
| Number of Gangs | 1.0 |
| Number of Switches | 1.0 |
| Poles | Single Pole |
| Switch Type | Paddle |
| Voltage | 120/277 V |

Material, Color, and Finish

| | |
|-------|-------|
| Color | Black |
|-------|-------|

Dimensions and Weight

| | |
|-----------|--------|
| Size | 4.2 in |
| Thickness | 1.5 in |

Descriptions

| | |
|------------------------|---|
| Description | RADIANT SWITCH 1P 15A 120/277V BK |
| extra long description | P&S TM870BK RADIANT SWITCH 1P 15A 1 |
| Long Description | Decorator Switch1Pole 15Amp 120/277V Grounding, Black |
| Product Type | Radiant Switch 1P 15A 120/277V BK |
| Special Features | Designer style, smooth quiet paddle action |

Manufacturer Information

| | |
|---------------------------|------------------------|
| Brand | LEGRAND-PASS & SEYMOUR |
| GTIN | 00785007245363 |
| Manufacturers Part Number | TM870BK |
| UPC | 785007245363 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------|
| Category Description | Residential Switches |
| Type | SWITCH |

Trade Size

| | |
|----------|------|
| Amperage | 15.0 |
|----------|------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight Per each | 0.14 |

Uses, Certifications, and Standards

| | |
|-------------|------------------------|
| Application | Residential/Commercial |
| Mounting | WALL |
| standard | UL, CULUS, UL 498, 20 |