



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 832361 12-10 VNL Ins Ringterm

*Ideal*

|                  |  |
|------------------|--|
| Catalog Number   | 832361   |
| Manufacturer     | Ideal  |
| Description      | Ideal, Ring Terminal, Vinyl Ring, Cable Size: 12 - 10 Awg, Number Of Holes: 1, Stud Size: 5/16 In, Material: Tin Plated Brass, Insulation: Vinyl Insulated |
| Weight per unit  | 0.0080 (lbs/each)  |
| Product Category | Small Terminals & Connectors   |

### Features

|                 |                  |
|-----------------|------------------|
| Cable Size      | 12 - 10          |
| insulation      | Vinyl Insulated  |
| Material        | TIN PLATED BRASS |
| Number of Holes | 1                |
| Stud Size       | 5/16             |

### Descriptions

|                        |   |
|------------------------|---|
| Description            | 12-10 VNL INS RINGTERM  |
| extra long description | IDEAL 83-2361 TRM VIN RNG 12-10 AWG   |
| Features               | Butted seam-construction prevents splitting under maximum pressureInternal barrel serrations grip wires tightly to resist pull-out and reduce electrical resistanceTin-plated brass construction for corrosion resistanceShouldered barrel insulation quickly positions terminal for proper crimpingExpanded insulation entry accommodates a wide variety of insulation diameters and provides additional insulation supportThe complete line of IDEAL crimp terminals, disconnects, and splices offer the right product for an |
| Long Description       | IDEAL, Ring Terminal, Vinyl Ring, Cable Size: 12 - 10 AWG, Number Of Holes: 1, Stud Size: 5/16 IN, Material: Tin Plated Brass, Insulation: Vinyl Insulated  |
| Product Type           | TRM Vin RNG 12-10 AWG5 16-25PK  |
| Special Features       | Features: Butted Seam-Construction Prevents Splitting Under Maximumpressure; Internal Barrel Serrations Grip Wires Tightly To Resist Pull-Out And Reduce Electrical Resistance; Tin Plated Brass Construction For Corrosion Resistance; Shouldered Barrel Insulation Quickly Positions Terminal For Proper Crimping; Expanded Insulation Entry Accomodates A Wide Variety Of Insulation Diameters And Provides Additional Insulation Support; Color-Coded Insulation And Wire Range Stamped On Terminal For Easy Identification |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Ideal          |
| GTIN                      | 00783250489893 |
| Manufacturers Part Number | 83-2361        |
| UPC                       | 783250489893   |

## Taxonomies, Classifications, and Categories

|                      |                            |
|----------------------|----------------------------|
| Category Description | TERMINAL BLOCK ACCESSORIES |
| Type                 | Vinyl Ring                 |

## Packaging

|                 |       |
|-----------------|-------|
| Carton          | 250   |
| Weight Per each | 0.008 |

## Uses, Certifications, and Standards

|          |                 |
|----------|-----------------|
| standard | UL Listed, RoHS |
|----------|-----------------|