



## DIMENSIONS<sup>(1)</sup>



NOMINAL LENGTH	A	B
T5	1 1/16" (27mm)	5" (127mm)
T8	1 1/4" (32mm)	4 1/2" (114mm)
T12	1 3/4" (32mm)	5 1/8" (131mm)

## DESCRIPTION

The Metalux Residential Thin Profile Undercabinet fixture provides effective task and enhancement lighting solutions for any decor. The series incorporates the latest Energy Efficient Technology, T5 fluorescent lamps and a ribbed acrylic diffuser to efficiently improve the appearance and productivity of the illuminated environment. Fixture lighting can be directed from under cabinets, shelves or overhead areas. The unique low profile design of the undercabinet fixture conforms to various applications such as kitchens, offices, study areas, displays, computer work centers and practically any undercounter installation where an inconspicuous light source is required.



## MAGNETIC UNDERCABINET SERIES

12", 21", 24", 33" or 42" Undercabinet

### RESIDENTIAL MAGNETIC UNDERCABINET SERIES

- Uses one T5, T8 OR T12 fluorescent lamp (included)
- Low profile
- 100% acrylic Tab-Loc Lens
- Pull chain (some models)
- Photocontrol LED Night Light (some models)
- Baked white enamel finish
- Suitable for damp locations
- UL/CUL Listed



## CLOSET LIGHT

1 Lamp 18" Fluorescent  
RESIDENTIAL  
LOW PROFILE

- Uses one T8 fluorescent lamp (not included)
- Low profile
- White ribbed acrylic diffuser/easily removed
- Pull chain
- Baked white enamel finish
- Suitable for damp locations
- UL/CUL Listed


## ORDERING INFORMATION<sup>(2)</sup>

Catalog Number	Description	Shipping Wt.
<b>Ultra Slim T5 Magnetic Undercabinets (With Rocker Switch)</b>		
8108R	12", 1 Lamp, T5, 8 Watt, Direct Wire, With Rocker Switch 2 lbs. (0.9kg)	
8213R	21", 1 Lamp, T5, 13 Watt, Direct Wire, With Rocker Switch	5 lbs. (2.3kg)
8316R	24", 2 Lamp, T5, 8 Watt, Direct Wire, With Rocker Switch	7 lbs. (3.2kg)
8421R	33", 1 Lamp(T5-8W),1 Lamp(T5-13W), With Rocker Switch	5 lbs. (2.3kg)
8526R	42", 2 Lamp, T5, 13 Watt, With Rocker Switch	9 lbs. (4.1kg)
<b>(With Rocker Switch and Cord &amp; Plug)</b>		
8108RCE	12", 1 Lamp, T5, 8 Watt, Direct Wire, With Rocker Switch and Cord & Plug	2 lbs. (0.9kg)
8213RCE	21", 1 Lamp, T5, 13 Watt, Direct Wire, With Rocker Switch and Cord & Plug	5 lbs. (2.3kg)
8316RCE	24", 2 Lamp, T5, 8 Watt, Direct Wire, With Rocker Switch and Cord & Plug	7 lbs. (3.2kg)
8421RCE	33", 1 Lamp(T5-8W),1 Lamp(T5-13W), With Rocker Switch and Cord & Plug	5 lbs. (2.3kg)
8526RCE	42", 2 Lamp, T5, 13 Watt, With Rocker Switch and Cord & Plug	9 lbs. (4.1kg)
<b>Slim T8 Magnetic Undercabinets (With Pull Chain)</b>		
8600PC	18", 1 Lamp, T8, 15 Watt, Direct Wire, With Pull Chain	4 lbs. (1.8kg)
<b>(Metal, Special Features)</b>		
8600RCNLT	18", 1 Lamp, T8, 15 Watt, Direct Wire, With Rocker Switch and Cord & Plug and LED Night Light	4 lbs. (1.8kg)
<b>(Plastic, With Rocker Switch and Cord &amp; Plug)</b>		
6015	15", 1 Lamp, T5, Direct Wire, With Rocker Switch and Cord & Plug, Plastic	2 lbs. (0.9kg)
6018	18", 1 Lamp, T8, Direct Wire, With Rocker Switch and Cord & Plug, Plastic	2 lbs. (0.9kg)
6021	21", 1 Lamp, T8, Direct Wire, With Rocker Switch and Cord & Plug, Plastic	2 lbs. (0.9kg)
6018BKL	18", 1 Lamp, T8, 15 Watt, With Rocker Switch and Cord & Plug, Blacklight Fixture	2 lbs. (0.9kg)

## Standard T12 Magnetic Undercabinets (With Rocker Switch)

8615R	18", 1 Lamp, T12, 15 Watt, Direct Wire, With Rocker Switch	5 lbs. (2.3kg)
8720R	24", 1 Lamp, T12, 20 Watt, Direct Wire, With Rocker Switch	6 lbs. (2.7kg)
8830R	36", 1 Lamp, T12, 30 Watt, Direct Wire, With Rocker Switch	8 lbs. (3.6kg)
8940R	48", 1 Lamp, T12, 40 Watt, Direct Wire, With Rocker Switch	9 lbs. (4.1kg)
<b>(With Rocker Switch and Cord &amp; Plug)</b>		
8615RC	18", 1 Lamp, T12, 15 Watt, Direct Wire, With Rocker Switch and Cord & Plug	5 lbs. (2.3kg)
8720RC	24", 1 Lamp, T12, 20 Watt, Direct Wire, With Rocker Switch and Cord & Plug	6 lbs. (2.7kg)
8830RC	36", 1 Lamp, T12, 30 Watt, Direct Wire, With Rocker Switch and Cord & Plug	8 lbs. (3.6kg)
8940RC	48", 1 Lamp, T12, 40 Watt, Direct Wire, With Rocker Switch and Cord & Plug	9 lbs. (4.1kg)

## DIMENSIONS<sup>(1)</sup>



## DESCRIPTION

The Metalux Residential 18" Closet Light w/pull chain provides effective task or closet lighting solutions. The Closet Light uses a fluorescent T8 lamp with a ribbed acrylic diffuser. This fixture can be wall or ceiling mounted. The low profile design of the closet light conforms to various applications such as over shelves or in low ceilings.

## ORDERING INFORMATION<sup>(2)</sup>

Catalog Number	Description	Shipping Wt.
<b>18" UNDERCABINETS</b>		
8600PC	18" length, 1 lamp, T8, 15 Watt w/pull chain	4 lbs. (1.8kg)

NOTE: <sup>(1)</sup> Specifications & dimensions subject to change without notice. <sup>(2)</sup> Consult your Cooper Lighting Representative for availability and ordering information.