

LEVELS

Patent Pending

**MAGNET
TRACK**

ULTRA
POWERFUL
Rare-Earth Magnets



**KLEIN
TOOLS**
For Professionals... Since 1857™



PROFESSIONAL-GRADE BILLET ALUMINUM LEVELS

Precision machined for high-accuracy leveling

Prevent dog-legs in conduit bends

Unique 3-point attachment to securely hold to conduit



HIGH-VISIBILITY ORANGE
won't get lost on conduit

Patent Pending

MAGNET TRACK

Permanently locks magnets to levels

ULTRA POWERFUL
Rare-Earth Magnets

EASY-TO-READ
vials with top-view windows

LIGHTS UP!

SUPER BRIGHT
HIGH-DEFINITION
LED VIALS

Tapered nose easily slides into pockets and fits in tighter spaces

ACCU-BEND™ 4-VIAL LEVEL
935AB4V

ACCU-BEND™ 1-VIAL LEVEL
(does not include magnets)
935AB1V

Top V-Groove fits contour of pipe



BILLET ALUMINUM TORPEDO LEVEL
935RB

LIGHTED BILLET TORPEDO LEVEL
935RBLT





ALUMINUM TORPEDO LEVEL

935R

- Tough aluminum frame
- Ultra powerful rare-earth magnets with locking track
- High-visibility orange body

TORPEDO LEVEL

935

- High-visibility orange body
- Strip magnet



Levels available in 6-pack
COUNTER DISPLAYS!*

*935 not available in a display

	Cat No.	UPC 0-92644+	Description	Vials	Magnet	Length	Weight
	935	93500-8	Torpedo Level	Level, 90°, 45°	Strip Magnet	9" (229 mm)	.26 lbs. (118 g)
	935R	93501-5	Aluminum Torpedo Level	Level, 90°, 45°	Ultra Powerful Rare-Earth	9" (229 mm)	.55 lbs. (249 g)
	935RB	93502-2	Billet Aluminum Torpedo Level	Level, 90°, 45°, 30°	Ultra Powerful Rare-Earth	8" (203 mm)	.45 lbs. (204 g)
	935RBLT	93503-9	Lighted Billet Aluminum Torpedo Level	Level, 90°, 45°	Ultra Powerful Rare-Earth	9" (229 mm)	.66 lbs. (299 g)
	935AB1V	93506-0	Accu-Bend™ 1-Vial Level	90°	N/A	2.5" (64 mm)	.15 lbs. (68 g)
	935AB4V	93507-7	Accu-Bend™ 4-Vial Level	Level, 90°, 45°, 30°	Ultra Powerful Rare-Earth	6.25" (159 mm)	.37 lbs. (168 g)

LEVELS

Patent Pending

MAGNET TRACK

ULTRA
POWERFUL
Rare-Earth Magnets



KLEIN TOOLS
EST. 1857
For Professionals... Since 1857™



PROFESSIONAL-GRADE BILLET ALUMINUM LEVELS

Precision machined for high-accuracy leveling

Prevent dog-legs in conduit bends

Unique 3-point attachment to securely hold to conduit



HIGH-VISIBILITY ORANGE
won't get lost on conduit

Patent Pending

MAGNET TRACK

Permanently locks magnets to levels

ULTRA POWERFUL
Rare-Earth Magnets

EASY-TO-READ
vials with top-view windows

LIGHTS UP!

SUPER BRIGHT
HIGH-DEFINITION
LED VIALS

ACCU-BEND™
4-VIAL LEVEL
935AB4V

ACCU-BEND™
1-VIAL LEVEL
(does not include magnets)
935AB1V

Top V-Groove fits contour of pipe

Tapered nose easily slides into pockets and fits in tighter spaces

BILLET ALUMINUM TORPEDO LEVEL
935RB

LIGHTED BILLET TORPEDO LEVEL
935RBLT





ALUMINUM TORPEDO LEVEL

935R

- Tough aluminum frame
- Ultra powerful rare-earth magnets with locking track
- High-visibility orange body

TORPEDO LEVEL

935

- High-visibility orange body
- Strip magnet



Levels available in 6-pack
COUNTER DISPLAYS!*

*935 not available in a display

	Cat No.	UPC 0-92644+	Description	Vials	Magnet	Length	Weight
	935	93500-8	Torpedo Level	Level, 90°, 45°	Strip Magnet	9" (229 mm)	.26 lbs. (118 g)
	935R	93501-5	Aluminum Torpedo Level	Level, 90°, 45°	Ultra Powerful Rare-Earth	9" (229 mm)	.55 lbs. (249 g)
	935RB	93502-2	Billet Aluminum Torpedo Level	Level, 90°, 45°, 30°	Ultra Powerful Rare-Earth	8" (203 mm)	.45 lbs. (204 g)
	935RBLT	93503-9	Lighted Billet Aluminum Torpedo Level	Level, 90°, 45°	Ultra Powerful Rare-Earth	9" (229 mm)	.66 lbs. (299 g)
	935AB1V	93506-0	Accu-Bend™ 1-Vial Level	90°	N/A	2.5" (64 mm)	.15 lbs. (68 g)
	935AB4V	93507-7	Accu-Bend™ 4-Vial Level	Level, 90°, 45°, 30°	Ultra Powerful Rare-Earth	6.25" (159 mm)	.37 lbs. (168 g)