



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



A24H2408GQRLP3PT 24.19X24.19X8 N4X FG 3PT LTCH HC *Hoffman Enclosures, Inc.*

| | |
|------------------|---|
| Catalog Number | A24H2408GQRLP3PT |
| Manufacturer | Hoffman Enclosures, Inc. |
| Description | Hinge Cover Enclosure 3-Point Type 4X, 24.19X24.19X8.00, Gray, Fiberglass |
| Weight per unit | 32.0 (lbs/each) |
| Product Category | Nema Types 4, 4X, 12 & 13 |

Features

| | |
|-----------|------------|
| ip rating | IP66 |
| Material | Fiberglass |

Material, Color, and Finish

| | |
|--------|--------------|
| Color | Gray |
| Finish | Smooth Matte |

Dimensions and Weight

| | |
|--------|---------------------|
| Depth | 8 |
| Height | 24.19 |
| Size | 24.19x24.19x8.00 in |
| Width | 24.19 |

Descriptions

| | |
|------------------------|--|
| Description | 24.19X24.19X8 N4X FG 3PT LTCH HC |
| extra long description | NVENT HOF A24H2408GQRLP3PT FG WALL |
| Features | A full range of modification options are available for wall-mount fiberglass enclosures, including variable depths to accommodate larger controls. These enclosures feature padlockable polyester latches, or HOFFMAN's exclusive PowerGlide Handle with 3-point latching, for ease of access with increased security. |
| Long Description | Hinge Cover Enclosure 3-Point Type 4X, 24.19x24.19x8.00, Gray, Fiberglass |
| Product Type | FG Wall MT Type 4X 3 PT |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Nvent Hoffman |
| GTIN | 00783510143565 |
| Manufacturers Part Number | A24H2408GQRLP3PT |
| UPC | 783510143565 |

Taxonomies, Classifications, and Categories

| | |
|------|---|
| Type | Fiberglass and Thermoplastic Wall Mounted Industrial Enclosures |
|------|---|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|----|
| Carton | 1 |
| Weight Per each | 32 |

Uses, Certifications, and Standards

| | |
|-------------|---|
| Application | Corrosive Environments; Controls and Drives |
| nema rating | 4X Watertight, corrosion-resistant |