



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **A0044200 12/2 WG MC Sol BK/WH/GN Alu Armor 250'** *Afc Cable*

Catalog Number	A0044200
Manufacturer	Afc Cable
Description	12-2 Solid - Black, White, Green - MC Glide Lite™ Plain Interlocked Aluminum Armor - Type MC - 250' Coil
Weight per unit	0.1050 (lbs/each)
Product Category	Wire

### **Features**

Bend Radius	6.9
Conductor Size	12
gauge	12 AWG
Inside Diameter	0.315
Material	Aluminum
media	Yes
Number of Conductors	3
outside diameter	0.46
Voltage Rating	600V

### **Material, Color, and Finish**

Color	Aluminum
Conductor Material	Copper

### **Dimensions and Weight**

Length	3000
--------	------

### **Descriptions**

Description	12/2 WG MC SOL BK/WH/GN ALU ARMOR 250'
extra long description	AFC A004-42-00 12-2 MCGLAL 250C
Features	Atkore's MC Glide is a Metal Clad (Type MC) Cable with a low-profile interlocked armor design that reduces worker fatigue and speeds up installation. Like its predecessor, MC Lite, MC Glide Lite has an aluminum interlocked armor that provides mechanical protection. These cables have no conductor count limit, offer various conductor bundle combinations, and meet UL Standard 1569 and NEC 330. They consist of THHN/THWN rated conductors twisted and wrapped with polypropylene assembly tape, and come with an ins
Long Description	12-2 Solid - Black, White, Green - MC Glide Lite™ Plain Interlocked Aluminum Armor - Type MC - 250' Coil
Product Type	12-2 McGlal 250C
Short Description	12-2 MCGLAL 250C



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	AFC CABLE SYSTEMS
GTIN	00077680351524
Manufacturers Part Number	A004-42-00
UPC	077680351524

## Taxonomies, Classifications, and Categories

Category Description	BX & MC
Type	Metal Clad Aluminum Armored Cable

## Trade Size

Trade Size	12-2
------------	------

## Packaging

Carton	250
Weight	543.84
Weight Per foot	0.105

## Uses, Certifications, and Standards

standard	UL 83, 1479, 1569, 1581, 2556, File Reference E80042.NEC® 230.43, 300.22(C), 392, 396, 330, 501, 502, 503, 530, 504, 505, 518, 520, 530, 645.Federal Specification A-A-59544 (formerly J-C-30B),Meets OSHA and HUD Requirements
Temperature Rating	194