



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

210 Veterans Avenue
75672-0000, TX Marshall
Phone: 903-935-9535
Fax: 903-935-3490



A20H1608SSLP Wallmount, Hinged With Nema Clamps, Type 4X, 20X16 *Hoffman Enclosures, Inc.*

| | |
|------------------|---|
| Catalog Number | A20H1608SSLP |
| Manufacturer | Hoffman Enclosures, Inc. |
| Description | Wallmount Hinged With Nema Clamps Type 4X, 20X16X8, Brushed, SS304 |
| Weight per unit | 33.0 (lbs/each) |
| Product Category | Nema Types 4 & 4X Metallic Enc |

Features

| | |
|-----------|-----------------|
| ip rating | IP66 |
| Material | Stainless Steel |

Material, Color, and Finish

| | |
|--------|------------|
| Color | Unpainted |
| Finish | Brushed #4 |

Dimensions and Weight

| | |
|--------|---------------------|
| Depth | 8 |
| Height | 20 |
| Size | 20.00x16.00x8.00 in |
| Width | 16 |

Descriptions

| | |
|------------------------|---|
| Description | WALLMOUNT, HINGED WITH NEMA CLAMPS, TYPE 4X, 20X16 |
| extra long description | NVENT HOF A20H1608SSLP Stainless En |
| Features | For use in indoor and outdoor corrosive environments that require a water-tight seal, this enclosure's seamless foam-in-place gasket and screw-down clamps provide a secure seal against contaminants. |
| Long Description | Wallmount Hinged with NEMA Clamps Type 4X, 20x16x8, Brushed, SS304 |
| Product Type | Stainless Encl. 20.00X16.00X8. |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Nvent Hoffman |
| GTIN | 00783510290207 |
| Manufacturers Part Number | A20H1608SSLP |
| UPC | 783510290207 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | STEEL JUNCTION BOXES |
| Type | Stainless Steel Wall Mounted Industrial Enclosures |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

210 Veterans Avenue
75672-0000, TX Marshall
Phone: 903-935-9535
Fax: 903-935-3490

Packaging

| | |
|-----------------|----|
| Carton | 1 |
| Weight Per each | 33 |

Uses, Certifications, and Standards

| | |
|-------------|---|
| Application | Controls and Drives; Corrosive Environments |
| nema rating | 4X Watertight, corrosion-resistant |