

ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5018 W Main Street 74701-0000, OK Durant Phone: 580-745-5448 Fax: 580-745-5449



Size

AE110L 110 CFM 1.3 Sones Led Fan/Light *Broan/Nutone LLC*

Catalog Number	AE110L
Manufacturer	Broan/Nutone LLC
Description	Bath Fan and Light, Ceiling Type; 9-1/4 Inch Length X 10 Inch Width X 5-3/4 Inch Height Size; UI, Hvi Approval; 120 Volt At 60 Hertz Voltage Rating; 0.3 Amp Current Rating; Yes Lamp Included; Led Lamp Type; 11 Watt Lamp Wattage
Weight per unit	9.1 (lbs/each)
Product Category	Exhaust Fans
atures	
Air Flow Rate	110 CFM
Current Rating	0.3 Amp
Duct Shape	Round
Duct Size	4 Inch Diameter
Grill Finish	White Polymeric
Grill Shape	Rectangular
Grill Size	11-3/4 Inch Length x 12-1/2 Inch Width
Housing Shape	Rectangular
Lamp Included	Yes
Lamp Type	LED
Lamp Wattage	11 Watt
Sound Level	1.3 SONES
Ventilation Area	105 Square Foot
Voltage Rating	120 Volt at 60 Hertz
aterial, Color, and Finish	
Housing Material	Rugged 26 Gauge Galvanized Steel

9-1/4 Inch Length x 10 Inch Width x 5-3/4 Inch Height



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5018 W Main Street 74701-0000, OK Durant Phone: 580-745-5448 Fax: 580-745-5449

Descriptions	
Additional Information	Power Rating 23.4 Watt; Number of Speed 1; Includes Permanently Lubricated Plug-In Motor, Tapered Sleeve, Non-Metallic Damper; Excludes Metallic Clatter; Standard Package 1 per pack
Commodity Description	Exhaust Fans
Description	110 CFM 1.3 SONES LED FAN/LIGHT
extra long description	CEILING TYPE; 9-1/4 INCH LENGTH X 10 INCH WIDTH X 5-3/4 INCH HEIGHT SIZE; UL, HVI APPROVAL; 120 VOLT AT 60 HERTZ VOLTAGE RATING; 0.3 AMP CURRENT RATING; YES LAMP INCLUDED; LED LAMP TYPE; 11 WATT LAMP WATTAGE; RUGGED 26 GAUGE GALVANIZED STEEL HOUSING MATERIAL; 110 CFM AIR FLOW RATE; 4 INCH DIAMETER DUCT SIZE; 1.3 SONES SOUND LEVEL; 11-3/4 INCH LENGTH X 12-1/2 INCH WIDTH GRILL SIZE; RECTANGULAR HOUSING SHAPE; ROUND DUCT SHAPE; RECTANGULAR GRILL SHAPE; WHITE POLYMERIC GRILL FINISH; 105 SQUARE FOOT VENTILATION
Long Description	BATH FAN AND LIGHT, CEILING TYPE; 9-1/4 INCH LENGTH X 10 INCH WIDTH X 5-3/4 INCH HEIGHT SIZE; UL, HVI APPROVAL; 120 VOLT AT 60 HERTZ VOLTAGE RATING; 0.3 AMP CURRENT RATING; YES LAMP INCLUDED; LED LAMP TYPE; 11 WATT LAMP WATTAGE
Product Type	Bath Fan and Light
Manufacturer Information	
Brand	Broan/Nutone LLC
GTIN	00026715236664
Manufacturers Part Number	AE110L
UPC	026715236664
Taxonomies, Classifications, and Cate	egories
Category Description	FANS & HEATERS
Туре	CEILING
Packaging	
Carton	1
Weight Per each	9.07
Uses, Certifications, and Standards Approval	UL, HVI