



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



AF202TRW 20A AfcI TR Rec W

Pass & Seymour/Legrand

| | |
|------------------|---|
| Catalog Number | AF202TRW |
| Manufacturer | Pass & Seymour/Legrand |
| Description | AfcI Outlets From The Radiant® Collection Detect and Cut Power During Arc-Fault Occurrences, Reducing The Risk Of Electrical Fires. Meeting National Electrical Code As An Alternative to AfcI Breakers, These Outlets Make It Easier to Recognize and Fix Trips Right Where They Happen. Maximize Safety, In Style, With AfcI Protection Featuring The Sleek, Clean Lines Of Radiant. 20A Outlets Are Ideal For Use With Larger Appliances, As Well As to Meet Regional Requirements (Chicago, Canada). Made Exclusively For |
| Weight per unit | 0.3000 (lbs/each) |
| Product Category | Gen Purpose Recept & Surge Pro |

Features

| | |
|------------------|------------------------|
| actuator | Control Circuit |
| amperage rating | 20 |
| connection | Back and side wire |
| Connection Type | Wired |
| indoor/outdoor | Indoor |
| interrupt rating | 4 to 6 mA |
| media | Yes |
| Mounting Type | Box |
| Number of Gangs | 1.0 |
| Outlet Type | AFCI, Tamper-Resistant |
| Output Current | 20A |
| Output Voltage | 125 V |
| Poles | 2 |
| trip range | 4 to 6 mA |
| Trip Type | .025 Second Nominal |
| Voltage Rating | 125 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Construction | Thermoplastic |
| Description | 20A AFCI TR REC W |
| extra long description | P&S AF202TRW DISC SUB AF203TRW |
| Features | Indicator Lights |
| Long Description | AFCI outlets from the radiant® Collection detect and cut power during arc-fault occurrences, reducing the risk of electrical fires. Meeting National Electrical Code as an alternative to AFCI breakers, these outlets make it easier to recognize and fix trips right where they happen. Maximize safety, in style, with AFCI protection featuring the sleek, clean lines of radiant. 20A outlets are ideal for use with larger appliances, as well as to meet regional requirements (Chicago, Canada). Made exclusively for |
| Product Type | Disc Sub Af203trw |
| Special Features | Pass & Seymour® Arc Fault Circuit Interrupter (AFCI) Receptacles are the latest innovation in electrical safety technology, and a Code-approved alternative to AFCI breakers. AFCI receptacles protect against electrical fires by detecting arc faults and de-energizing the circuit. |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Pass & Seymour |
| GTIN | 00785007127881 |
| Manufacturers Part Number | AF202TRW |
| UPC | 785007127881 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------------------|
| Category Description | Residential Switches |
| Type | Tamper-Resistant, AFCI |

Trade Size

| | |
|----------|------|
| Amperage | 20.0 |
|----------|------|

Availability

| | |
|--------|----------|
| Status | Inactive |
|--------|----------|

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Weight Per each | 0.3 |

Uses, Certifications, and Standards

| | |
|--------------------------|---|
| Application | Commercial/Residential |
| environmental conditions | 0 to 95% (relative humidity, non-condensing) |
| Frequency Rating | 60 Hz |
| standard | UL, CSA, cULus Listed 1699A, File #E363109, Federal Specification WC596. UL498, Standard CSA-C22.2 No. 42 |