



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## A80 80 CFM 2.0 Sones Fan

Broan/Nutone LLC

|                  |   |
|------------------|---|
| Catalog Number   | A80   |
| Manufacturer     | Broan/Nutone LLC  |
| Description      | Ventilation Fan, Rugged 26 Gauge Galvanized Steel, Ceiling Mount, 120 V Ac @ 60 HZ, 43.1 W, 0.37 A, 80 CFM Air Flow, 60 HZ, Round Duct Shape, 4 In Duct Size, White, Polymeric Grill Material, Rectangular Grill Shape, 11-3/8 In (L) X 12 In (W) Grill Size, Rugged 26 Gauge Galvanized Steel Housing Material, Rectangular Housing Shape, Permanently Lubricated Plug-In Motor, 9-1/4 In Overall Length, 10 In Overall Width, 5-3/4 In Overall Height, 4 In Duct Diameter, Exhaust, 8.75 LB |
| Weight per unit  | 8.8 (lbs/each)  |
| Product Category | Exhaust Fans  |

### Features

|                  |                |
|------------------|----------------|
| Air Flow Rate    | 80 CFM         |
| Sound Level      | 2 SONES        |
| Ventilation Area | 75 Square Foot |

### Dimensions and Weight

|      |   |
|------|---|
| Size | 9-1/4 Inch Length x 10 Inch Width x 5-3/4 Inch Height |
|------|---|

### Descriptions

|                        |   |
|------------------------|---|
| Additional Information | Power Rating 43.1 Watt; Efficacy Rating 1.89 CFM/Watt; Duct Direction Horizontal; Includes Permanently Lubricated Plug-In Motor, Blower Wheel   |
| Commodity Description  | Exhaust Fans  |
| Description            | 80 CFM 2.0 SONES FAN  |
| extra long description | CEILING TYPE; 9-1/4 INCH LENGTH X 10 INCH WIDTH X 5-3/4 INCH HEIGHT SIZE; UL, HVI APPROVAL; 120 VOLT AC 60 HERTZ VOLTAGE RATING; 0.37 AMP CURRENT RATING; 26 GAUGE GALVANIZED STEEL HOUSING MATERIAL; 80 CFM AIR FLOW RATE; 4 INCH DIAMETER DUCT SIZE; 2 SONES SOUND LEVEL; 11-3/8 INCH LENGTH X 12 INCH WIDTH GRILL SIZE; POLYMERIC GRILL MATERIAL; RECTANGULAR HOUSING SHAPE; ROUND DUCT SHAPE; RECTANGULAR GRILL SHAPE; WHITE GRILL FINISH; 75 SQUARE FOOT VENTILATION AREA; FLEX[™] SERIES BRAND; POWER RATING 43.1 WATT; |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

|       |                |
|-------|----------------|
| Brand | BROAN          |
| GTIN  | 00026715236510 |
| UPC   | 026715236510   |

## Taxonomies, Classifications, and Categories

|                      |                  |
|----------------------|------------------|
| Category Description | FANS & HEATERS   |
| Type                 | Ceiling, 1-Speed |

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Weight Per each | 8.75 |

## Uses, Certifications, and Standards

|          |         |
|----------|---------|
| Approval | UL, HVI |
|----------|---------|