



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ABC30R 30A 125V 1/4X1-1/4 Fa Ceramic Fuse

Bussmann Fuses

| | |
|------------------|---|
| Catalog Number | ABC30R |
| Manufacturer | Bussmann Fuses |
| Description | Eaton Agc Series Fast-Acting Fuse, 9A, 250 Vac, 32 VDC (Self Certified) |
| Weight per unit | 0.0100 (lbs/each) |
| Product Category | Small Dimension Fuses |

Features

| | |
|--------------------|---|
| amperage rating | 30 A |
| connection | Ferrule End X Ferrule End |
| dimensions | 1.2835 IN X 0.2520 IN X 0.2520 IN |
| interrupt rating | 1000 AIC at 125 Vac400 AIC at 125 Vdc1 kAIC at 75 Vdc200 AIC at 250 Vac |
| Material | Nickel-plated brass endcapsCeramic tube |
| Response Time | 4 hr at 100%, 60 min at 135%, 120 sec at 200% |
| type of indicators | Non-Indicating |
| Voltage Rating | 250 Vac, 125 Vdc, 32 Vac (self certified) |

Dimensions and Weight

| | |
|------|-----------------------------------|
| Size | 1/4 In Diameter X 1-1/4 In Length |
|------|-----------------------------------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|--|
| Description | 30A 125V 1/4X1-1/4 FA CERAMIC FUSE |
| extra long description | EFSE ABC-30-R ROHS COMPLIANT |
| Features | Fast-acting, ceramic tube 1/4" x 1-1/4" ferrule fuse designed to UL 248-14 for overcurrent protection of electronic circuits. Install into a Bussmann Series fuse holder, block, or fuse clip, or purchase with available axial leads for thru-hole installation. Eaton's ABC fast-acting, ceramic body tube 1/4" x 1-1/4" fuses are designed with higher interrupting ratings and voltage ratings to UL 248-14 for overcurrent protection of electronic circuits. This is a RoHS compliant fuse. Order in cartridge fuse form |
| Long Description | Eaton AGC series Fast-acting fuse, 9A, 250 Vac, 32 Vdc (self certified) |
| Product Type | Rohs Compliant |
| Special Features | Interrupt Rating 200 Amp at 250 Vac, 1000 Amp at 125 Vac, 400 Amp at 125 Vdc, 1000 Amp at 75 Vdc, Material Ceramic Tube, Nickel Plated Brass Endcap |

Manufacturer Information

| | |
|---------------------------|-----------------------|
| Brand | Eaton Bussmann series |
| GTIN | 00051712542487 |
| Manufacturers Part Number | ABC-30-R |
| UPC | 051712542487 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------------------|
| Category Description | GLASS FUSES (and ceramic) |
| Type | Fast-Acting Fuse |

Packaging

| | |
|-----------------|------|
| Carton | 5 |
| Weight Per each | 0.01 |

Uses, Certifications, and Standards

| | |
|-------------|--|
| Application | Ind Facilities & Factories - Facility: Safety and Security Systems |
| standard | CE Marked,RoHS Compliant |