



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ABMMAC 0.75" X 0.75" NylN CBL Tie Adh Mount WHT *Panduit Corporation*

Catalog Number	ABMMAC
Manufacturer	Panduit Corporation
Description	Panduit'S Abmm-A-C Rubber-Based Adhesive Back Cable Tie Mounts Have Been Designed For Fast Installation and Long-Term Performance. These Mounts Can Be Used With Miniature and Intermediate Cables Ties. Made Of Abs Plastic and Intended For Use In Indoor Environments. They Are 0.75" X 0.75" (19.1MM X 19.1MM), Supplied In Strips Of 2, Are White In Color and Come In Packages Of 100.
Weight per unit	0.0004 (lbs/each)
Product Category	Cable Ties & Wraps

Features

Cable Size	NA
Cable Type	Cable Tie Mount
insulation	Other
Material	ABS
Temperature Range	-20°F - 120°F (-29°C - 49°C)

Material, Color, and Finish

Color	White
-------	-------

Descriptions

Description	0.75" X 0.75" NYL N CBL TIE ADH MOUNT WHT
extra long description	PAN ABMM-A-C ABMM-A-C Cable Tie Mou
Long Description	Panduit's ABMM-A-C rubber-based adhesive back cable tie mounts have been designed for fast installation and long-term performance. These mounts can be used with miniature and intermediate cables ties. Made of ABS plastic and intended for use in indoor environments. They are 0.75" x 0.75" (19.1mm x 19.1mm), supplied in strips of 2, are white in color and come in packages of 100.
Product Type	Abmm-A-C Cable Tie Mount, White, Abs, Rubber Adh., 0.75X0.75

Manufacturer Information

Brand	PANDUIT
GTIN	00074983585007
Manufacturers Part Number	ABMM-A-C
UPC	074983585007

Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	Cable Tie Mount



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

minimum qty 100

Packaging

Carton 100

Package 500

Weight Per each 0.0004

Uses, Certifications, and Standards

Application Indoor

Mounting Adhesive Tape

Operating Temperature 120

standard CE Compliant, UL Recognized: E136577, RoHS Compliant