



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ACP1044CD 100A 4W4P P&S Plug (600VAC/250VDC) *Appleton/Oz Gedney*

| | |
|------------------|--|
| Catalog Number | ACP1044CD |
| Manufacturer | Appleton/Oz Gedney |
| Description | Pin and Sleeve Plug, 100 A, 600 V Ac 3 Phase @ 50 to 400 HZ 250 V DC, 4 Poles, 4 Wires, Epoxy Powder Coated Copper Free Aluminum, -40 °C Operating Temperature, +107 °C Operating Temperature, Pressure Wire Terminal, #4 to #1 Awg (Building);#4 to #2 Awg (Extra Flex) Wire Size, 5 LB |
| Weight per unit | 5.0 (lbs/each) |
| Product Category | Pin & Sleeve Devices |

Features

| | |
|-----------------|------------------------|
| amperage rating | 100 |
| connection | Pressure Wire Terminal |
| Number of Wires | 4 |
| Phase | 3 |
| Poles | 4 |

Descriptions

| | |
|------------------------|---|
| Description | 100A 4W4P P&S PLUG (600VAC/250VDC) |
| extra long description | APP ACP1044CD 100A CLAMP RING PLUG |
| Special Features | Designed to supply power to portable or fixed electrical equipment such as motor generator units, welders, pumps, compressors, cellular relay stations and similar apparatus;Grounding style: Shell only;Ideal for use on shipping docks, ports and other ship to shore applications;Locking screw and slot prevents plug cable collar from backing off;Natural finish glass filled polyester insulating blocks;Plug and receptacle combination is NEMA 4X rated when clamping ring is fully tightened on receptacle;Rough usag |

Manufacturer Information

| | |
|-------|----------------|
| Brand | Appleton |
| GTIN | 00781381440172 |
| UPC | 781381440172 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------------------------|
| Category Description | Pin & Sleeve Devices |
| Type | Grounding Style 1 Clamping Ring Plug |

Packaging

| | |
|-----------------|---|
| Carton | 6 |
| Weight Per each | 5 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|--------------------------|---|
| Application | For ADR1044 Receptacle And ARC1044CD Connector Body |
| environmental conditions | Temperature Rating: -40 To 107 DEG C |
| standard | CSA Certified: 065179;CSA Standard: C22.2 No. 182.1;NEMA FB11;UL 1682, UL 1686, UL 50E;UL Listed: E145916, E145917 |