



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



AGC1610R 1-6/10A 250V 1/4X1-1/4 Rohs Fa Glass Fuse

Bussmann Fuses

| | |
|------------------|--|
| Catalog Number | AGC1610R |
| Manufacturer | Bussmann Fuses |
| Description | Eaton Agc Series Fast-Acting Fuse 1.6A, 250 Vac, 32 VDC (Self Certified), Agc-1-6-10-R |
| Weight per unit | 0.0060 (lbs/each) |
| Product Category | Small Dimension Fuses |

Features

| | |
|------------------|--|
| amperage rating | 1.6A |
| connection | Ferrule End X Ferrule End |
| dimensions | 1.2500 IN X 0.2500 IN X 0.2500 IN |
| interrupt rating | 100 AIC at 250 Vac10 kAIC at 125 Vac |
| Material | Glass tubeNickel-plated brass end cap construction |
| Response Time | 60 min at 135%, 120 sec at 200% |
| Voltage Rating | 250 Vac, 32 Vdc (self certified) |

Dimensions and Weight

| | |
|------|-----------------------------------|
| Size | 1/4 In Diameter X 1-1/4 In Length |
|------|-----------------------------------|

Descriptions

| | |
|------------------------|--|
| Description | 1-6/10A 250V 1/4X1-1/4 ROHS FA GLASS FUSE |
| extra long description | EFSE AGC-1-6/10-R BUSS SMALL DIMENS |
| Features | Fast-acting, glass tube 1/4" x 1-1/4" ferrule fuse designed to UL 248-14 for overcurrent protection of electronic circuits. Install into a Bussmann Series fuse holder, block, or fuse clip, or purchase with available axial leads for thru-hole installation. Eaton's AGC fast-acting, glass tube 1/4" x 1-1/4" ferrule fuses are designed to UL 248-14 for overcurrent protection of electronic circuits. Order in cartridge fuse format and install into a Bussmann Series fuse holder, block, or fuse clip, or purchase w |
| Long Description | Eaton AGC series Fast-acting fuse 1.6A, 250 Vac, 32 Vdc (self certified), AGC-1-6-10-R |
| Product Type | Buss Small Dimension Fuse |
| Special Features | Interrupt Rating 100 Amp at 250 Vac, 10000 Amp at 250 Vac, Material Glass Tube, Nickel Plated Brass Endcap, ROHS Compliant |

Manufacturer Information

| | |
|---------------------------|-----------------------|
| Brand | Eaton Bussmann series |
| GTIN | 00051712654869 |
| Manufacturers Part Number | AGC-1-6/10-R |
| UPC | 051712654869 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------|
| Category Description | GLASS FUSES (and ceramic) |
| Type | Fast-acting glass tube fuse |

Packaging

| | |
|-----------------|-------|
| Carton | 5 |
| Weight Per each | 0.006 |

Uses, Certifications, and Standards

| | |
|-------------|--|
| Application | Ind Facilities & Factories - Facility: Safety and Security Systems |
| standard | CE Marked, RoHS Compliant |