



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## AGC5 5A 250V 1/4X1-1/4 Rohs Fa Glass Fuse *Bussmann Fuses*

|                  |                                     |
|------------------|-------------------------------------|
| Catalog Number   | AGC5                                |
| Manufacturer     | Bussmann Fuses                      |
| Description      | Buss Agc-5 Agc Glass Fuse - 1/4 X 1 |
| Weight per unit  | 0.0070 (lbs/each)                   |
| Product Category | Tools & Testers                     |

### Features

|                    |                                               |
|--------------------|-----------------------------------------------|
| amperage rating    | 5 Amp                                         |
| connection         | Ferrule End X Ferrule End                     |
| Response Time      | 60 Min Maximum at 135%, 120 S Maximum at 200% |
| type of indicators | Non-Indicating                                |
| Voltage Rating     | 250 VAC                                       |

### Dimensions and Weight

|      |                                   |
|------|-----------------------------------|
| Size | 1/4 In Diameter X 1-1/4 In Length |
|------|-----------------------------------|

### Descriptions

|                  |                                                                                                               |
|------------------|---------------------------------------------------------------------------------------------------------------|
| Description      | 5A 250V 1/4X1-1/4 ROHS FA GLASS FUSE                                                                          |
| Long Description | BUSS AGC-5 AGC GLASS FUSE - 1/4 x 1                                                                           |
| Product Type     | Agc Glass Fuse - 1/4 X 1-1/4 - 5 Amp                                                                          |
| Special Features | Interrupt Rating 200 Amp at 250 Vac, 10000 Amp at 125 Vac,<br>Material Glass Tube, Nickel Plated Brass Endcap |

### Manufacturer Information

|                           |                               |
|---------------------------|-------------------------------|
| Brand                     | Cooper Bussmann North America |
| GTIN                      | 00051712703888                |
| Manufacturers Part Number | AGC-5                         |
| UPC                       | 051712703888                  |

### Taxonomies, Classifications, and Categories

|                      |                           |
|----------------------|---------------------------|
| Category Description | GLASS FUSES (and ceramic) |
| Type                 | Electronic, Fast Acting   |

### Availability

|                     |          |
|---------------------|----------|
| Manufacturer Status | Inactive |
| Status              | Inactive |

### Packaging

|                 |       |
|-----------------|-------|
| Carton          | 5     |
| Weight Per each | 0.007 |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

---

## Uses, Certifications, and Standards

Application  
standard

Electronic Circuits  
UL 248-14, CSA