



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## AYCL153PHIV Ariadni 150W Led 3WAY Ivory Clam

Lutron

|                  |   |
|------------------|---|
| Catalog Number   | AYCL153PHIV   |
| Manufacturer     | Lutron  |
| Description      | Dimmable Bulb, Toggle Switch Type, 120 V, 150 W;6000 W, 60 HZ, Incandescent/Halogen;Dimmable CFL/Led Lamp, Motion Sensor, Wall Mount, 2.86 In Length, 2.58 In Width, 4.60 In Height, Ivory, +32 °F Operating Temperature, +104 °F Operating Temperature, 1 Yr Warranty, 0.4 LB/Ea |
| Weight per unit  | 0.4000 (lbs/each)   |
| Product Category | Lighting Dimmers  |

### Features

|                 |                |
|-----------------|----------------|
| actuator        | Toggle Switch  |
| connection      | Screw Terminal |
| Connection Type | Screw Terminal |
| insulation      | Plastic        |
| Material        | Plastic/Metal  |
| Poles           | 1              |
| Voltage Rating  | 120            |
| Wattage         | 600            |

### Material, Color, and Finish

|        |       |
|--------|-------|
| Finish | Gloss |
|--------|-------|

### Dimensions and Weight

|      |                      |
|------|----------------------|
| Size | 4.60 x 2.86;117 x 73 |
|------|----------------------|

### Descriptions

|                        |  |
|------------------------|--|
| Description            | ARIADNI 150W LED 3WAY IVORY CLAM   |
| extra long description | LUT AYCL-153PH-IV ARIADNI CFL/LED D  |
| Features               | The Ariadni LED+ dimmer provides optimal dimming performance of LED bulbs. This dimmer works with up to 150-Watt of dimmable LED/CFL or 600-Watt of incandescent/halogen, allowing you to control multiple bulb types on the same circuit. It is designed to control a broad range of dimmable LED and CFL bulbs from a variety of brands including Philips, Cree, GE, EcoSmart and Lighting Science. The Ariadni dimmer features a toggle switch to turn your lights off or on-returning the lights to your favorite level. A |
| Special Features       | Controls 150 W LED/CFL (screw-base) or 600 W incandescent/halogen loads. Toggle turn lights on/off. Slide up to brighten, down to dim. Provides reliable dimming of dimmable LEDs/CFLs as well as halogens and incandescents.  |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

|      |                |
|------|----------------|
| GTIN | 00027557826044 |
| UPC  | 027557826044   |

## Taxonomies, Classifications, and Categories

|                      |  |
|----------------------|--|
| Category Description | Residential dimmers, motion sensors, controls, & photo cells |
| Type                 | Preset dimmer, 3-way/single-pole, clamshell packaging        |

## Packaging

|                 |     |
|-----------------|-----|
| Carton          | 3   |
| Package         | 48  |
| Weight Per each | 0.4 |

## Uses, Certifications, and Standards

|                          |                             |
|--------------------------|-----------------------------|
| Application              | Lighting Control            |
| Enclosure                | Plastic                     |
| environmental conditions | Indoor use only             |
| Mounting                 | WALLBOX                     |
| Operating Temperature    | 32 to 104                   |
| standard                 | UL1472 CSA C22.2 184.1, NOM |