



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



AYCL253PWH Ariadni 250W Led 3WAY White

Lutron

| | |
|------------------|---|
| Catalog Number | AYCL253PWH |
| Manufacturer | Lutron |
| Description | Ariadni Dimmer For 250W CFL/Led, 600W Inc/Hal, or Lutron Hi-Lume A-Series Lte Led Driver In White |
| Weight per unit | 0.3500 (lbs/each) |
| Product Category | Lighting Dimmers |

Features

| | |
|-----------------|----------------|
| actuator | Toggle Switch |
| connection | Screw Terminal |
| Connection Type | Screw Terminal |
| insulation | Plastic |
| Material | Plastic/Metal |
| media | Yes |
| Poles | 1 |
| Switch Type | Toggle |
| Voltage Rating | 120 |
| Wattage | 600 |

Material, Color, and Finish

| | |
|--------|-------|
| Color | White |
| Finish | Gloss |

Dimensions and Weight

| | |
|------|----------------------|
| Size | 4.60 x 2.86;117 x 73 |
|------|----------------------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | ARIADNI 250W LED 3WAY WHITE |
| extra long description | LUT AYCL-253P-WH ARIADNI CFL/LED 25 |
| Features | The Ariadni LED+ dimmer switch works with dimmable LED and CFL screw-in bulbs up to 250-Watt and is also compatible with up to 600-Watt of standard incandescent and halogen bulbs, allowing you to control all 4 bulb types on the same circuit. It is designed to control a broad range of dimmable LED and CFL bulbs from a variety of brands including Philips, Cree, GE, Eco Smart and Lighting Science. The Ariadni/Toggler LED+ dimmer switch matches your existing toggle switches. It features a slider to adjust your |
| Long Description | Ariadni dimmer for 250W CFL/LED, 600W inc/hal, or Lutron Hi-Lume A-Series LTE LED Driver in white |
| Product Type | Ariadni CFL/Led 250W White |
| Special Features | Controls 250 W LED/CFL (screw-base), 600 W incandescent/halogen or 350 W Hi-Lume 1 percent 2-wire LED driver loads. Toggle turn lights on/off. Slide up to brighten, down to dim. Provides reliable dimming of dimmable LEDs/CFLs as well as halogens and incandescents. |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Lutron |
| GTIN | 00784276090100 |
| Manufacturers Part Number | AYCL253PWH |
| UPC | 784276090100 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | Residential dimmers, motion sensors, controls, & photo cells |
| Type | Preset dimmer, 3-way/single-pole |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight Per each | 0.35 |

Uses, Certifications, and Standards

| | |
|--------------------------|---|
| Application | Lighting Control |
| Enclosure | Plastic |
| environmental conditions | 0 to 90% humidity, non-condensing. Indoor use only. |
| Mounting | WALLBOX |
| Operating Temperature | 32 to 104 |
| standard | UL1472 CSA C22.2 184.1, NEMA SSL-7A Type 2 |