



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## AY600PNLIV Ariadni 600W SP Nlite Ivory

Lutron



|                  |  |
|------------------|--|
| Catalog Number   | AY600PNLIV   |
| Manufacturer     | Lutron   |
| Description      | 00027557670425 0027557 027557670425 02755767042 67042 Ay 600PNL Iv Ay-600PNL-1V AY600PNLIV Ay-600PNL-1v Ariadni 600W Preset W/Night Light Ivory Lewtron Electronics Ay 600PNL Iv Lewtron Electronics Ay-600PNL-1V Lewtron Electronics AY600PNLIV Lewtron Electronics Ay-600PNL-1v Lootron Electronics Ay 600PNL Iv Lootron Electronics Ay-600PNL-1V Lootron Electronics AY600PNLIV Lootron Electronics Ay-600PNL-1v Lutron Ay 600PNL Iv Lutron Ay-600PNL-1V Lutron AY600PNLIV Lutron Ay-600PNL-1v Lutron Electric Ay 600PNL Iv |
| Weight per unit  | 0.2000 (lbs/each)  |
| Product Category | Lighting Dimmers   |

### Features

|                |                |
|----------------|----------------|
| actuator       | Toggle Switch  |
| Coil Voltage   | 48.000 48.000  |
| connection     | Screw Terminal |
| insulation     | Plastic        |
| Material       | METAL/PLASTIC  |
| Poles          | 1              |
| Voltage Rating | 120            |
| Wattage        | 600            |

### Material, Color, and Finish

|       |       |
|-------|-------|
| Color | Ivory |
|-------|-------|

### Dimensions and Weight

|      |                                    |
|------|------------------------------------|
| Size | 4.60 in (117 mm) x 2.86 in (73 mm) |
|------|------------------------------------|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                  |  |
|------------------|--|
| Description      | ARIADNI 600W SP NLITE IVORY  |
| Long Description | 00027557670425   0027557   027557670425   02755767042   67042   AY 600PNL IV   AY-600PNL-1V   AY600PNLIV   AY-600PNL-IV   ARIADNI 600W PRESET W/NIGHT LIGHT IVORY   Lewtron Electronics AY 600PNL IV   Lewtron Electronics AY-600PNL-1V   Lewtron Electronics AY600PNLIV   Lewtron Electronics AY-600PNL-IV   Lootron Electronics AY 600PNL IV   Lootron Electronics AY-600PNL-1V   Lootron Electronics AY600PNLIV   Lootron Electronics AY-600PNL-IV   Lutron AY 600PNL IV   Lutron AY-600PNL-1V   Lutron AY600PNLIV   Lutron AY-600PNL-IV   LUTRON ELECTRIC AY 600PNL IV |
| Product Type     | Obsolete-Ay 600W Preset W/Night Light Iv   |
| Special Features | Controls 600 W incandescent or halogen loads. Toggle turns lights on/off. Slide up to brighten, down to dim. Includes amber locator light.   |

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Lutron         |
| GTIN                      | 00027557670425 |
| Manufacturers Part Number | AY-600PNL-IV   |
| sub brand                 | Ariadni        |
| UPC                       | 027557670425   |

## Taxonomies, Classifications, and Categories

|                      |  |
|----------------------|--|
| Category Description | Residential dimmers, motion sensors, controls, & photo cells |
| Type                 | Preset dimmer with locator light, single-pole                |

## Availability

|                     |          |
|---------------------|----------|
| Manufacturer Status | Inactive |
| Status              | Inactive |

## Packaging

|                 |     |
|-----------------|-----|
| Carton          | 1   |
| Weight Per each | 0.2 |

## Uses, Certifications, and Standards

|                          |                         |
|--------------------------|-------------------------|
| Application              | Lighting Control        |
| Enclosure                | Plastic                 |
| environmental conditions | Indoor use only         |
| Frequency Rating         | 50-60                   |
| Mounting                 | WALLBOX                 |
| Operating Temperature    | 32 to 104 F (0 to 40 C) |
| standard                 | UL, cUL                 |