



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## AYCL153PIV Ariadni 150W Led 3WAY Ivory

Lutron

Catalog Number	AYCL153PIV
Manufacturer	Lutron
Description	Dimmable Bulb, Toggle Switch Type, 120 V, 150 W;6000 W, 60 HZ, Incandescent/Halogen;Dimmable CFL/Led Lamp, Motion Sensor, Wall Mount, 2.86 In Length, 2.58 In Width, 4.60 In Height, Ivory, +32 °F Operating Temperature, +104 °F Operating Temperature, 1 Yr Warranty, 0.2 LB/Ea
Weight per unit	0.2000 (lbs/each)
Product Category	Lighting Dimmers

### Features

actuator	Toggle Switch
connection	Screw Terminal
Connection Type	Screw Terminal
insulation	Plastic
Material	Plastic/Metal
Poles	1
Voltage Rating	120
Wattage	600

### Material, Color, and Finish

Finish	Gloss
--------	-------

### Dimensions and Weight

Size	4.60 x 2.86;117 x 73
------	----------------------

### Descriptions

Description	ARIADNI 150W LED 3WAY IVORY
extra long description	LUT AYCL-153P-IV ARIADNI CFL/LED DI
Features	The Ariadni LED+ dimmer provides optimal dimming performance of LED bulbs. This dimmer works with up to 150-Watt of dimmable LED/CFL or 600-Watt of incandescent/halogen, allowing you to control multiple bulb types on the same circuit. It is designed to control a broad range of dimmable LED and CFL bulbs from a variety of brands including Philips, Cree, GE, EcoSmart and Lighting Science. The Ariadni dimmer features a toggle switch to turn your lights off or on-returning the lights to your favorite level. A
Special Features	Controls 150 W LED/CFL (screw-base) or 600 W incandescent/halogen loads. Toggle turn lights on/off. Slide up to brighten, down to dim. Provides reliable dimming of dimmable LEDs/CFLs as well as halogens and incandescents.



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

GTIN	00027557825979
UPC	027557825979

## Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Preset dimmer, 3-way/single-pole

## Packaging

Carton	1
Weight Per each	0.2

## Uses, Certifications, and Standards

Application	Lighting Control
Enclosure	Plastic
environmental conditions	Indoor use only
Mounting	WALLBOX
Operating Temperature	32 to 104
standard	UL1472 CSA C22.2 184.1, NOM