



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## B2011SS4114RGD BLTD 1-1/4" SS4 Rigid Pipe Clamp

*Cooper B-Line/Cable Tray*

Catalog Number	B2011SS4114RGD
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series O.D. Pipe and Conduit Clamp, 0.0740" H X 3.3510" L X 1.25" W, Steel, 600 LBS Load Cap
Weight per unit	0.2000 (lbs/each)
Product Category	Channel & Strut Fittings

### Features

dimensions	3.3510 IN X 1.2500 IN X 0.0740 IN
Material	304 Stainless Steel

### Material, Color, and Finish

Finish	STAINLESS STEEL TYPE 304
--------	--------------------------

### Dimensions and Weight

Size	1-1/4 in
------	----------

### Descriptions

Construction	TWO PIECE
Description	BLTD 1-1/4" SS4 RIGID PIPE CLAMP
extra long description	B-LINE B2011SS4 1 1/4"-RIGID CONDUIT
Features	Eaton offers a wide variety of B-Line series pipe clamps and accessories used for the support and attachment of pipe to structural members.
Long Description	Eaton B-Line series O.D. pipe and conduit clamp, 0.0740" H x 3.3510" L x 1.25" W, Steel, 600 Lbs load cap
Product Type	1 1/4"-Rigid Conduit Clamp, 1 1/4", SSL 304
Special Features	Includes Combination Recess Hex Head Machine Screw and Square Nut

### Manufacturer Information

Brand	Eaton
GTIN	00781011601331
Manufacturers Part Number	B2011SS4
UPC	781011601331

### Taxonomies, Classifications, and Categories

Category Description	BEAM, RA, EDGE, & PARALLEL CLAMPS
Type	O.D. pipe and conduit clamp

### Availability

Status	Inactive
--------	----------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	50
Weight Per each	0.2

## Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
Mounting standard	CHANNEL Not Applicable