



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3706 Frankston Hwy  
75701-0000, TX Tyler  
Phone: 903-509-9882  
Fax: 903-509-9832



## **BAB1020 Type Bab Circuit BRKR 1P, 20AMP 120/240V, 10, 000AIC,** *Eaton Corp*

Catalog Number	BAB1020
Manufacturer	Eaton Corp
Description	Eaton Bab Thermal Magnetic Circuit Breaker, Quicklag Industrial Thermal-Magnetic Circuit Breaker, Bolt-On Mounting, High Intensity Discharge, 20 A, 10 Kaic, Single-Pole, 120/240 V, Non-Interchangeable, Q7, Bab
Weight per unit	0.3500 (lbs/each)
Product Category	1 Pole Standard Trip Bolt-On

### Features

dimensions	3.0000 IN X 1.0000 IN X 2.5000 IN
interrupt rating	10
media	Yes
Poles	Single-pole
Voltage Rating	120/240 V

### Descriptions

Description	TYPE BAB CIRCUIT BRKR 1P,20AMP 120/240V,10,000AIC,
extra long description	ETN BAB1020 BAB 1P,20AMP, 120/240V,
Features	Eaton's bolt-on miniature circuit breakers (Quicklag) provide superior protection in panelboards, and offer easy installation. They are also switching duty rated for 120 VAC fluorescent light applications, and UL 489 listed. All products 15-100A are HACR rated. Select from one-, two-, or three-pole designs.
Long Description	Eaton BAB thermal magnetic circuit breaker,Quicklag industrial thermal-magnetic circuit breaker,Bolt-on mounting, High intensity discharge,20 A,10 kAIC,Single-pole,120/240 V,Non-Interchangeable,Q7,BAB
Product Type	Bab 1P, 20AMP, 120/240V, 10, 000AIC, 40C,
Special Features	Bolt-on mountingHigh intensity discharge

### Manufacturer Information

Brand	Eaton
GTIN	00786679301203
Manufacturers Part Number	BAB1020
UPC	786679301203

### Taxonomies, Classifications, and Categories

Category Description	PANELBOARD BRANCH BREAKERS
Type	Thermal magnetic circuit breakers



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3706 Frankston Hwy  
75701-0000, TX Tyler  
Phone: 903-509-9882  
Fax: 903-509-9832

## Availability

Status ..... Inactive .....

## Packaging

Carton ..... 1 .....

Package ..... 24 .....

Weight Per each ..... 0.35 .....

## Uses, Certifications, and Standards

Application ..... OtherGeneration - Renewable Energy - Alternative  
EnergyGeneration - Conventional Energy - Conventional  
EnergyDatacenters - IT Space: CI and Hyper ConvergedMarine  
Vessels and Equipment - Marine Vessels and Equipment -  
OtherResidential Bldgs & Facilities - Residential Bldgs & Facilities -  
Other .....

standard ..... CSA Certified,UL Listed .....