

## ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

9172 E Florentine Road Unit 9 86314-0000, AZ Prescott Valley Phone: 928-356-1174 Fax: 480-426-8084



## **B2213PAZN BLTD 2" Zinc Plated Pre-Assembled Unv Pipe Clamp** Cooper B-Line/Cable Tray

Catalog Number	B2213PAZN
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Multi-Grip and Offset Pipe Clamp, 0.0966" H X 4" L X 1.25" W, Steel, 600 LBS Load Cap, Pipe Clamp For Thinwall (Emt)
Weight per unit	0.2600 (lbs/each)
Product Category	Channel & Strut Fittings
eatures	
dimensions	4.0000 IN X 1.2500 IN X 0.0966 IN
Material	12 Gauge Low Carbon Steel
Material, Color, and Finish	
Finish	Zinc Plated
Dimensions and Weight	
Size	2 in
Descriptions	
Construction	TWO PIECE
Description	BLTD 2" ZINC PLATED PRE-ASSEMBLED UNV PIPE CLAMP
extra long description	B-LINE B2213PAZN 2"-MULTI-GRIP PIPE
Features	Eaton offers a wide variety of B-Line series pipe clamps and accessories used for the support and attachment of pipe to structural members.
Long Description	Eaton B-Line series multi-grip and offset pipe clamp, 0.0966" H x 4" L x 1.25" W, Steel, 600 Lbs load cap, Pipe clamp for thinwall (EMT)
Product Type	2"-Multi-Grip Pipe Clamp, Pre-Asm, Thinwall IMC Rigid, 2", Z
Special Features	Includes Combination Recess Hex Head Machine Screw and Square Nut, Pipe Range 2.192 To 2.400 In OD, Load Capacity 600 Lb Vertical, 75 Lb Transverse
/lanufacturer Information	
Brand	Eaton
GTIN	00781011604646
Manufacturers Part Number	B2213PAZN
UPC	781011604646

## Taxonomies, Classifications, and Categories

Category Description	BEAM, RA, EDGE, & PARALLEL CLAMPS
Туре	Multi-grip and offset pipe clamp



standard

## ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

9172 E Florentine Road Unit 9 86314-0000, AZ Prescott Valley Phone: 928-356-1174 Fax: 480-426-8084

1
50
0.26
Commercial / Institutional Buildings / Structures - Commercial /
Institutional Buildings / Structures - Other
CHANNEL

Not Applicable