



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

711 Lake Bardwell Dr.  
75119-0000, TX Ennis  
Phone: 972-875-3413  
Fax: 972-875-3174



## BAF2 2A 250V Midget Fuse

*Bussmann Fuses*

Catalog Number	BAF2
Manufacturer	Bussmann Fuses
Description	Eaton Bussmann Series Baf Fuse, Fast Acting, 2 A, Non-Indicating, Ferrule End X Ferrule End, 10 Kaic At 125 Vac, 100 Aic At 250 Vac, Nickel-Plated Brass Endcaps, Standard, 250 V
Weight per unit	0.2500 (lbs/each)
Product Category	Small Dimension Fuses

### Features

amperage rating	2 AMP
class	Supplemental
connection	Ferrule End X Ferrule End
dimensions	1.5000 IN X 0.4100 IN X 0.4100 IN
interrupt rating	100 Amp at 250 Vac, 10000 Amp at 125 Vac
Material	Nickel-plated brass endcaps
media	Yes
Voltage Rating	250 VAC

### Dimensions and Weight

Size	13/32 In Diameter X 1-1/2 In Length
------	-------------------------------------

### Descriptions

Description	2A 250V MIDGET FUSE
extra long description	BUSS BAF-2 BUSS MIDGET FUSE
Features	Bussmann offers the broadest selection of Supplemental and Midget fuses in both time-delay and fast-acting designs with voltages as high as 600Vac and 600Vdc.
Long Description	Eaton Bussmann series BAF fuse, Fast acting, 2 A, Non-indicating, Ferrule end x ferrule end, 10 kAIC at 125 Vac, 100 AIC at 250 Vac, Nickel-plated brass endcaps, Standard, 250 V
Product Type	Buss Midget Fuse
Special Features	Nickel Plated Brass Endcap

### Manufacturer Information

Brand	Eaton Bussmann series
GTIN	00051712320023
Manufacturers Part Number	BAF-2
UPC	051712320023

### Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	FUSE



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

711 Lake Bardwell Dr.  
75119-0000, TX Ennis  
Phone: 972-875-3413  
Fax: 972-875-3174

## Packaging

Carton	1
Package	10
Weight Per each	0.25

## Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Safety and Security Systems
standard	CE Marked