



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **BKLGE500T Main BKR Kit 480V Max 1 / 3PH 500A LG Top Mounting**

*Eaton Corp*

Catalog Number	BKLGE500T
Manufacturer	Eaton Corp
Description	Main BKR Kit 480V Max 1 or 3PH 500A LG Top Mounting
Weight per unit	7.0 (lbs/each)
Product Category	Accessories

### **Features**

amperage rating	500A
dimensions	5.5000 IN X 5.5000 IN X 12.0000 IN
media	Yes
Phase	Single-phase, three-phase
Short Circuit Rating	35
Voltage Rating	277 V, 480 V

### **Descriptions**

Description	MAIN BKR KIT 480V MAX 1 / 3PH 500A LG TOP MOUNTING
extra long description	ETN BKLGE500T MAIN BKR KIT 480V 1_3
Features	Panelboards Pow-R-Stock Plus Program provide interiors; type 1 and 3R boxes; surface and flush trims; factory-assembled panelboards; main breaker kits; branch breakers; lug kits; service entrance kits; ground kits; and 200% neutral kits. In addition, the distributor stocking program can be used with various Eaton commercial distribution products and is designed to meet UL67 standards for use in data center, industrial, commercial and healthcare facilities.
Long Description	MAIN BKR KIT 480V MAX 1 OR 3PH 500A LG TOP MOUNTING
Product Type	Main BKR Kit 480V 1_3PH 500A LG Top MNT

### **Manufacturer Information**

Brand	Eaton
GTIN	00786687010814
Manufacturers Part Number	BKLGE500T
UPC	786687010814

### **Taxonomies, Classifications, and Categories**

Category Description	Breaker Connector and Mounting Kits & Other Accessories
Type	Accessory

### **Packaging**

Carton	1
Weight Per each	7



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	OtherElec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
Mounting	TOP
Operating Temperature standard	40°C UL Listed