



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BLD6089SWH 6" 10W Led Surface Mount 27-5K 812 Lumens

Cooper Lighting Solutions

Catalog Number	BLD6089SWH
Manufacturer	Cooper Lighting Solutions
Description	00800838267281 0008008 00800838267281 80083826728 26728 BLD6089SWH Cooper Lighting BLD6089SWH Cooper Lighting Solutions BLD6089SWH Cooper Lite BLD6089SWH
Weight per unit	1.2 (lbs/each)
Product Category	Led Recessed Architectural & S

Features

amperage rating	90m
Ballast Type	N/A
Lamp Type	LED
Number of Lamps	1
Voltage Rating	120
Wattage	10 W

Material, Color, and Finish

Style	(blank)
-------	---------

Descriptions

Description	6" 10W LED SURFACE MOUNT 27-5K 812 LUMENS
extra long description	ETNCL-CAN BLD6089SWH BLD, 6 IN, 800
Long Description	00800838267281 0008008 00800838267281 80083826728 26728 BLD6089SWH Cooper Lighting BLD6089SWH Cooper Lighting Solutions BLD6089SWH Cooper Lite BLD6089SWH
Product Type	BLD, 6 In, 800 LM, 90 Cri Select CCT, WH
Special Features	Select from 5 CCTs via switch, 2700K, 3000K, 3500K, 4000K, 5000K CCT

Manufacturer Information

Brand	HALO
GTIN	00080083826728
Manufacturers Part Number	BLD6089SWH
sub brand	Prevail Series
UPC	080083826728

Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	BLD6 LED

Availability

Manufacturer Status	Inactive
Status	Inactive



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton 1

Weight Per each 1.2

Uses, Certifications, and Standards

Application lighting

Mounting Recessed

standard cULus Listed - Wet Location;Airtite;RoHS Compliant;Energy
Star;Title 20 Compliant;Title 24 Compliant;Showerlight;IECC
Compliant