



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **BR120ST Type BR BRKR 20A/1 Pole 120/240V 10K W/Shunt Trip** *Eaton Corp*

|                  |                                                                                                                                                                                                |
|------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number   | BR120ST                                                                                                                                                                                        |
| Manufacturer     | Eaton Corp                                                                                                                                                                                     |
| Description      | Eaton BR Thermal Magnetic Circuit Breaker, Type BR 1-Inch Plug-On Circuit Breaker, 20 A, 10 Kaic, Single-Pole, 120/240V, BR, #14-4 Awg Cu/Al, Q1, BR, Type BR Loadcenters, Shunt Trip Included |
| Weight per unit  | 0.6000 (lbs/each)                                                                                                                                                                              |
| Product Category | 1 Pole Standard Trip Plug-In                                                                                                                                                                   |

### **Features**

|                  |                                   |
|------------------|-----------------------------------|
| dimensions       | 2.5000 IN X 1.0000 IN X 2.0000 IN |
| interrupt rating | 10 kAIC                           |
| Poles            | 1                                 |
| Voltage Rating   | 120/240 V                         |

### **Descriptions**

|                        |                                                                                                                                                                                                                                                                                                                                                    |
|------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description            | TYPE BR BRKR 20A/1 POLE 120/240V 10K W/SHUNT TRIP                                                                                                                                                                                                                                                                                                  |
| extra long description | ETN BR120ST BR 20A/1 Pole 120/240V                                                                                                                                                                                                                                                                                                                 |
| Features               | Eaton's BR circuit breakers are used in indoor and outdoor BR loadcenters, spa panels, meter breakers and sub panels. They are designed for a wide range of applications such as high short-circuit interrupt, series rating combinations with upstream main breakers, thermal magnetic, AFCI, GFCI, equipment protection and dual function AF/GF. |
| Long Description       | Eaton BR thermal magnetic circuit breaker, Type BR 1-Inch plug-on circuit breaker, 20 A, 10 kAIC, Single-pole, 120/240V, BR, #14-4 AWG Cu/Al, Q1, BR, Type BR loadcenters, Shunt trip included                                                                                                                                                     |
| Product Type           | BR 20A/1 Pole 120/240V 10K W/Shunt Trip                                                                                                                                                                                                                                                                                                            |
| Special Features       | Shunt Trip                                                                                                                                                                                                                                                                                                                                         |

### **Manufacturer Information**

|                           |                |
|---------------------------|----------------|
| Brand                     | Eaton          |
| GTIN                      | 00786676000161 |
| Manufacturers Part Number | BR120ST        |
| UPC                       | 786676000161   |

### **Taxonomies, Classifications, and Categories**

|                      |                                             |
|----------------------|---------------------------------------------|
| Category Description | Specialty Breakers (Quad, Dupl, Shunt Trip) |
| Type                 | Thermal magnetic circuit breakers           |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

|                 |     |
|-----------------|-----|
| Carton          | 1   |
| Weight Per each | 0.6 |

## Uses, Certifications, and Standards

|             |                                                                                                                                                                                                                                         |
|-------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Application | OtherGeneration - Conventional Energy - Conventional<br>EnergyDatacenters - IT Space: CI and Hyper ConvergedMarine<br>Vessels and Equipment - Marine Vessels and Equipment -<br>OtherGeneration - Renewable Energy - Alternative Energy |
| standard    | UL 489,Federal Specifications Classification W-C375                                                                                                                                                                                     |