



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BR1624L125G Cut BR1624L125G 1PH/125ML/16-24/N1

Eaton Corp

Catalog Number	BR1624L125G
Manufacturer	Eaton Corp
Description	BR Style 1-Inch Loadcenter, Main Lug, Ground Bar, Includes BREQS125 Hold-Down Screw, 125A, Single-Phase, 24-Pole, 24 Circuits, 16 Spaces, 120/240V, #6-2/0 Awg Cu/Al At 60°C or 75°C Wire, Nema 1 Enclosure, B2 Box Size
Weight per unit	18.3 (lbs/each)
Product Category	Single Phase Main Lug Load Cen

Features

amperage rating	125 VAC
Box Size	SPC250L
cover	Cover included
Cover Type	Cover included
dimensions	98.5520millimetreX36.3474centimetreX47.6250centimetre
interrupt rating	10 kAIC
main circuit breaker	CEMAT RSRT9 V7.0 OS SOFTWARE
Number of Circuits	24 VDC
number of spaces	16 OZ
Number of Wires	Three-wire
Phase	1 PH
used with	Type BR 1-inch breakers
Voltage Rating	120/240 VAC
Wire Size	#6-2/0 AWG Cu/Al at 60°C or 75°C

Material, Color, and Finish

Bus Material	Aluminum
Enclosure Material	Metallic

Dimensions and Weight

Size	B2
------	----



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	CUT BR1624L125G 1PH/125ML/16-24/N1
extra long description	ETN BR1624L125G BR style 1-inch loa
Long Description	BR style 1-inch loadcenter, main lug, ground bar, includes BREQS125 hold-down screw, 125A, single-phase, 24-pole, 24 circuits, 16 spaces, 120/240V, #6-2/0 AWG Cu/Al at 60°C or 75°C wire, NEMA 1 enclosure, b2 box size
Product Type	BR Style 1-Inch Loadcenter
Special Features	Ground bar, includes BREQS125 hold-down screw

Manufacturer Information

Brand	Eaton
GTIN	00786676446808
Manufacturers Part Number	BR1624L125G
UPC	786676446808

Taxonomies, Classifications, and Categories

Category Description	LOADCENTER ACCESSORIES
igcc	PLUG, NON POLARIZED TYPE; THERMOPLASTIC MATERIAL; WHITE COLOR; 1-15P CONFIGURATION; UL 1706, CSA APPROVAL; 125 V VOLTAGE RATING; 15 AMPERE CURRENT RATING; IMPACT RESISTANT; (2) 18 AWG CORD SIZE; HOMeselect[T] BRAND
Type	MAIN LUG
unspsc code	39121101

Packaging

Carton	1
Weight Per each	18.3

Uses, Certifications, and Standards

Application	Power Distribution
Enclosure	NEMA 1
Mounting	Combination
standard	UL 67; UL 50