

Eaton BR60120B200R

Catalog Number: BR60120B200R

Main circuit breaker loadcenter,200A,Aluminum,NEMA 3R,120 circuits,60 spaces,Single-phase,Top/bottom,120/240V

General specifications



Product Name	Catalog Number
Eaton BR main breaker loadcenter	BR60120B200R
UPC	Product Length/Depth
786685931708	5.2 in
Product Height	Product Width
48.75 in	14.3 in
Product Weight	Warranty
50 lb	10 year
Compliances	Certifications
UL67	UL Listed file E52977

Product specifications

Type

Main circuit breaker loadcenter

Amperage Rating

200 A

Bus material

Aluminum

Number of circuits

120

Number of spaces

60

Phase

Single-phase

Feed type

Top/bottom

Voltage rating

120/240 V

Enclosure

NEMA 3R

Resources

Specifications and datasheets

[Eaton Specification Sheet - BR60120B200R](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton BR60120B200R

Catalog Number: BR60120B200R

Main circuit breaker loadcenter,200A,Aluminum,NEMA 3R,120 circuits,60 spaces,Single-phase,Top/bottom,120/240V

General specifications



Product Name	Catalog Number
Eaton BR main breaker loadcenter	BR60120B200R
UPC	Product Length/Depth
786685931708	5.2 in
Product Height	Product Width
48.75 in	14.3 in
Product Weight	Warranty
50 lb	10 year
Compliances	Certifications
UL67	UL Listed file E52977

Product specifications

Type

Main circuit breaker loadcenter

Amperage Rating

200 A

Bus material

Aluminum

Number of circuits

120

Number of spaces

60

Phase

Single-phase

Feed type

Top/bottom

Voltage rating

120/240 V

Enclosure

NEMA 3R

Resources

Specifications and datasheets

[Eaton Specification Sheet - BR60120B200R](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)