



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BRDC230240 BRDC Breaker 1-30/2P 1-40/2P Com. Trip 120/240V 10 *Eaton Corp*

Catalog Number	BRDC230240
Manufacturer	Eaton Corp
Description	Eaton BR Thermal Magnetic Circuit Breaker, Type BR 1-Inch Quad Circuit Breaker, (2) 30 A, (2) 40 A, 10 Kaic, Four-Pole, 120/240V, BRD, Common Breaker Trip, #14-4 Awg Cu/Al, BRD, Type BR Loadcenters
Weight per unit	0.8000 (lbs/each)
Product Category	Quadplex Standard Trip Plug-In

Features

dimensions	3.0000 IN X 2.0000 IN X 3.0000 IN
interrupt rating	10 kAIC
Poles	4
Trip Type	Common breaker trip
Voltage Rating	120/240 V

Descriptions

Description	BRDC BREAKER 1-30/2P 1-40/2P COM. TRIP 120/240V 10
extra long description	ETN BRDC230240 BRDC 1-30/2P 1-40/2P
Features	Eaton's BR circuit breakers are used in indoor and outdoor BR loadcenters, spa panels, meter breakers and sub panels. They are designed for a wide range of applications such as high short-circuit interrupt, series rating combinations with upstream main breakers, thermal magnetic, AFCI, GFCI, equipment protection and dual function AF/GF.
Long Description	Eaton BR thermal magnetic circuit breaker, Type BR 1-Inch quad circuit breaker, (2) 30 A, (2) 40 A, 10 kAIC, Four-pole, 120/240V, BRD, Common breaker trip, #14-4 AWG Cu/Al, BRD, Type BR Loadcenters
Product Type	BRDC 1-30/2P 1-40/2P 120/240V 10K

Manufacturer Information

Brand	Eaton
GTIN	00786676372336
Manufacturers Part Number	BRDC230240
UPC	786676372336

Taxonomies, Classifications, and Categories

Category Description	Specialty Breakers (Quad, Dupl, Shunt Trip)
Type	Thermal magnetic circuit breakers



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.8

Uses, Certifications, and Standards

Application	Generation - Renewable Energy - Alternative Energy Marine Vessels and Equipment - Marine Vessels and Equipment - Other Generation - Conventional Energy - Conventional Energy Other Datacenters - IT Space: CI and Hyper Converged
standard	UL 489, Federal Specifications Classification W-C375