

Specifications

Photo is representative



Eaton BRP16B100R

Eaton BR main breaker loadcenter, 100 A, X2, Aluminum, Cover included, NEMA 3R, Metallic, 10 kAIC, BR, 32 circuits, Single pole, 16 spaces, Three-wire, Single-phase, Combination, NEMA 3R, Type BR 1-inch breakers, 120/240V

Product specifications

| | |
|-----------------------------|---|
| TYPE | Plug-on neutral main circuit breaker loadcenter |
| AMPERAGE RATING | 100 A |
| BUS MATERIAL | Aluminum |
| COVER | Cover included |
| MAIN CIRCUIT BREAKER | BR |
| NUMBER OF CIRCUITS | 32 |
| NUMBER OF POLES | Single-pole |
| NUMBER OF SPACES | 16 |
| PHASE | Single-phase |
| MOUNTING | Combination |
| USED WITH | Type BR 1-inch breakers |
| VOLTAGE RATING | 120/240 V |
| BOX SIZE | X2 |
| ENCLOSURE | NEMA 3R |
| ENCLOSURE MATERIAL | Metallic |
| INTERRUPT RATING | 10 kAIC |
| NUMBER OF WIRES | 3 |
| NEMA RATING | NEMA 3R |

General specifications

| | |
|-----------------------------|----------------------------------|
| PRODUCT NAME | Eaton BR main breaker loadcenter |
| CATALOG NUMBER | BRP16B100R |
| UPC | 786689059194 |
| PRODUCT LENGTH/DEPTH | 21 in |
| PRODUCT HEIGHT | 5.5 in |
| PRODUCT WIDTH | 14.31 in |
| PRODUCT WEIGHT | 16 lb |
| WARRANTY | 10 year |
| CERTIFICATIONS | UL 50 UL 67 |

EATON

Powering Business Worldwide

Specifications

Photo is representative



Eaton BRP16B100R

Eaton BR main breaker loadcenter, 100 A, X2, Aluminum, Cover included, NEMA 3R, Metallic, 10 kAIC, BR, 32 circuits, Single pole, 16 spaces, Three-wire, Single-phase, Combination, NEMA 3R, Type BR 1-inch breakers, 120/240V

Product specifications

| | |
|-----------------------------|---|
| TYPE | Plug-on neutral main circuit breaker loadcenter |
| AMPERAGE RATING | 100 A |
| BUS MATERIAL | Aluminum |
| COVER | Cover included |
| MAIN CIRCUIT BREAKER | BR |
| NUMBER OF CIRCUITS | 32 |
| NUMBER OF POLES | Single-pole |
| NUMBER OF SPACES | 16 |
| PHASE | Single-phase |
| MOUNTING | Combination |
| USED WITH | Type BR 1-inch breakers |
| VOLTAGE RATING | 120/240 V |
| BOX SIZE | X2 |
| ENCLOSURE | NEMA 3R |
| ENCLOSURE MATERIAL | Metallic |
| INTERRUPT RATING | 10 kAIC |
| NUMBER OF WIRES | 3 |
| NEMA RATING | NEMA 3R |

General specifications

| | |
|-----------------------------|----------------------------------|
| PRODUCT NAME | Eaton BR main breaker loadcenter |
| CATALOG NUMBER | BRP16B100R |
| UPC | 786689059194 |
| PRODUCT LENGTH/DEPTH | 21 in |
| PRODUCT HEIGHT | 5.5 in |
| PRODUCT WIDTH | 14.31 in |
| PRODUCT WEIGHT | 16 lb |
| WARRANTY | 10 year |
| CERTIFICATIONS | UL 50 UL 67 |

EATON

Powering Business Worldwide