

Specifications

Photo is representative

Eaton BRP16L125R

Eaton Eaton BR main lug loadcenter, Main lug only, 125 A, X1, Aluminum, NEMA 3R, Metallic, 10 kAIC, BR, NEMA 3R, 32 Circuits, Single-pole, 16 Spaces, Three-wire, Single-phase, Type BR 1-inch breakers, 120/240V, #6-2/0

General specifications

PRODUCT NAME	Eaton BR main lug loadcenter
CATALOG NUMBER	BRP16L125R
UPC	786689059200
PRODUCT LENGTH/DEPTH	3.88 in
PRODUCT HEIGHT	18.75 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	15 lb
WARRANTY	10 year
CERTIFICATIONS	UL 67 UL 50

Product specifications		Resources	
TYPE	MLO	SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - BRP16L125R
AMPERAGE RATING	125 A		
BUS MATERIAL	Aluminum	WARRANTY GUIDES	Eaton type BR circuit breaker limited warranty June 2024
COVER	Cover included		
MAIN CIRCUIT BREAKER	BR		
NUMBER OF CIRCUITS	32		
NUMBER OF POLES	Single-pole		
NUMBER OF SPACES	16		
PHASE	Single-phase		
USED WITH	Type BR 1-inch breakers		
VOLTAGE RATING	120/240V		
BOX SIZE	X1		
ENCLOSURE	NEMA 3R		
ENCLOSURE MATERIAL	Metallic		
INTERRUPT RATING	10 kAIC		
NEMA RATING	NEMA 3R		
NUMBER OF WIRES	3		

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications

Photo is representative

Eaton BRP16L125R

Eaton Eaton BR main lug loadcenter, Main lug only, 125 A, X1, Aluminum, NEMA 3R, Metallic, 10 kAIC, BR, NEMA 3R, 32 Circuits, Single-pole, 16 Spaces, Three-wire, Single-phase, Type BR 1-inch breakers, 120/240V, #6-2/0

General specifications

PRODUCT NAME	Eaton BR main lug loadcenter
CATALOG NUMBER	BRP16L125R
UPC	786689059200
PRODUCT LENGTH/DEPTH	3.88 in
PRODUCT HEIGHT	18.75 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	15 lb
WARRANTY	10 year
CERTIFICATIONS	UL 67 UL 50

Product specifications		Resources	
TYPE	MLO	SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - BRP16L125R
AMPERAGE RATING	125 A		
BUS MATERIAL	Aluminum	WARRANTY GUIDES	Eaton type BR circuit breaker limited warranty June 2024
COVER	Cover included		
MAIN CIRCUIT BREAKER	BR		
NUMBER OF CIRCUITS	32		
NUMBER OF POLES	Single-pole		
NUMBER OF SPACES	16		
PHASE	Single-phase		
USED WITH	Type BR 1-inch breakers		
VOLTAGE RATING	120/240V		
BOX SIZE	X1		
ENCLOSURE	NEMA 3R		
ENCLOSURE MATERIAL	Metallic		
INTERRUPT RATING	10 kAIC		
NEMA RATING	NEMA 3R		
NUMBER OF WIRES	3		

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

