

Specifications



Eaton BRP20L150

Eaton Eaton BR main lug loadcenter, Main lug only, 150 A, X3, Aluminum, NEMA 1, Metallic, 10kAIC, CSR2125, NEMA 1, 40 Circuits, Twenty pole, 20 Spaces, Two hots, a neutral, and a ground, Single-phase, Type BR 1-inch breakers, 120/240V, #1–300 kcmil

General specifications

PRODUCT NAME	Eaton BR main lug loadcenter
CATALOG NUMBER	BRP20L150
UPC	786689053246
PRODUCT LENGTH/DEPTH	23 in
PRODUCT HEIGHT	3.88 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	21 lb
WARRANTY	10 year
CERTIFICATIONS	UL 50 UL 67



Product specifications

TYPE
AMPERAGE RATING
BUS MATERIAL
COVER
MAIN CIRCUIT BREAKER
NUMBER OF CIRCUITS
NUMBER OF POLES
NUMBER OF SPACES
PHASE
USED WITH
VOLTAGE RATING
BOX SIZE
ENCLOSURE
ENCLOSURE MATERIAL
INTERRUPT RATING
NEMA RATING
NUMBER OF WIRES

Specifications



Eaton BRP20L150

Eaton Eaton BR main lug loadcenter, Main lug only, 150 A, X3, Aluminum, NEMA 1, Metallic, 10kAIC, CSR2125, NEMA 1, 40 Circuits, Twenty pole, 20 Spaces, Two hots, a neutral, and a ground, Single-phase, Type BR 1-inch breakers, 120/240V, #1–300 kcmil

General specifications

PRODUCT NAME	Eaton BR main lug loadcenter
CATALOG NUMBER	BRP20L150
UPC	786689053246
PRODUCT LENGTH/DEPTH	23 in
PRODUCT HEIGHT	3.88 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	21 lb
WARRANTY	10 year
CERTIFICATIONS	UL 50 UL 67



Product specifications

TYPE
AMPERAGE RATING
BUS MATERIAL
COVER
MAIN CIRCUIT BREAKER
NUMBER OF CIRCUITS
NUMBER OF POLES
NUMBER OF SPACES
PHASE
USED WITH
VOLTAGE RATING
BOX SIZE
ENCLOSURE
ENCLOSURE MATERIAL
INTERRUPT RATING
NEMA RATING
NUMBER OF WIRES