



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BR125 Type BR BRKR 25A/1 Pole 120/240V 10K

Eaton Corp

Catalog Number	BR125
Manufacturer	Eaton Corp
Description	Eaton BR Thermal Magnetic Circuit Breaker, Type BR 1-Inch Plug-On Circuit Breaker, 25 A, 10 Kaic, Single-Pole, 120/240V, BR, #14-4 Awg Cu/Al, BR, Type BR Loadcenters
Weight per unit	0.3000 (lbs/each)
Product Category	1 Pole Standard Trip Plug-In

Features

dimensions	3.3000 IN X 1.6000 IN X 3.3000 IN
interrupt rating	10
Poles	1
Voltage Rating	120/240 V

Descriptions

Description	TYPE BR BRKR 25A/1 POLE 120/240V 10K
extra long description	ETN BR125 Type BR Breaker 25A/1 Pol
Features	Eaton's BR circuit breakers are used in indoor and outdoor BR loadcenters, spa panels, meter breakers and sub panels. They are designed for a wide range of applications such as high short-circuit interrupt, series rating combinations with upstream main breakers, thermal magnetic, AFCI, GFCI, equipment protection and dual function AF/GF.
Long Description	Eaton BR thermal magnetic circuit breaker, Type BR 1-Inch plug-on circuit breaker, 25 A, 10 kAIC, Single-pole, 120/240V, BR, #14-4 AWG Cu/Al, BR, Type BR Loadcenters
Product Type	Type BR Breaker 25A/1 Pole 120/240V 10K

Manufacturer Information

Brand	Eaton
GTIN	00786676362153
Manufacturers Part Number	BR125
UPC	786676362153

Taxonomies, Classifications, and Categories

Category Description	Loadcenter Plug In Breakers and Accessories
Type	Thermal magnetic circuit breakers

Packaging

Carton	1
Package	10
Weight Per each	0.3



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Generation - Renewable Energy - Alternative

EnergyOtherGeneration - Conventional Energy - Conventional

EnergyMarine Vessels and Equipment - Marine Vessels and

Equipment - OtherDatacenters - IT Space: CI and Hyper

Converged

standard

UL 489, Federal Specifications Classification W-C375