



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4955 Bell Springs Rd Unit 9
78620-0000, TX Dripping Springs
Phone: 737-317-5073
Fax: 737-317-5074



BR1620B100 16/20C 100A 1PH MB Loadcenter *Eaton Corp*

Catalog Number	BR1620B100
Manufacturer	Eaton Corp
Description	BR Style 1-Inch Loadcenter, Main Circuit Breaker, No Feed-Thru Lugs, 100A, Single-Phase, 20-Pole, 20 Circuits, 16 Spaces, 120/240V, #4-1/0 Awg Cu/Al At 60°C or 75°C Wire, Nema 1 Enclosure, C1 Box Size
Weight per unit	22.0 (lbs/each)
Product Category	Single Phase Main Breaker Load

Features

amperage rating	100 WTT
Box Size	08447
cover	Cover included
Cover Type	Cover included
dimensions	4.5000 IN X 15.5000 IN X 47.0000 IN
interrupt rating	10 kAIC
main circuit breaker	CEMAT RSRT9 V7.0 OS SOFTWARE
Number of Circuits	20 W
number of spaces	16 OZ
Number of Wires	Three-wire
Phase	1 PH
used with	Type BR 1-inch breakers
Voltage Rating	120/240 VAC
Wire Size	#4-1/0 AWG Cu/Al at 60°C or 75°C

Material, Color, and Finish

Bus Material	Aluminum
Enclosure Material	Metallic

Dimensions and Weight

Size	08447
------	-------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4955 Bell Springs Rd Unit 9
78620-0000, TX Dripping Springs
Phone: 737-317-5073
Fax: 737-317-5074

Descriptions

Description	16/20C 100A 1PH MB LOADCENTER
extra long description	ETN BR1620B100 BR style 1-inch load
Long Description	BR style 1-inch loadcenter, main circuit breaker, no feed-thru lugs, 100A, single-phase, 20-pole, 20 circuits, 16 spaces, 120/240V, #4-1/0 AWG Cu/Al at 60°C or 75°C wire, NEMA 1 enclosure, c1 box size
Product Type	BR Style 1-Inch Loadcenter
Special Features	No feed-thru lugs

Manufacturer Information

Brand	Eaton
GTIN	00786676444002
Manufacturers Part Number	BR1620B100
UPC	786676444002

Taxonomies, Classifications, and Categories

Category Description	LOADCENTERS & COVERS
igcc	PLUG, NON POLARIZED TYPE; THERMOPLASTIC MATERIAL; WHITE COLOR; 1-15P CONFIGURATION; UL 1706, CSA APPROVAL; 125 V VOLTAGE RATING; 15 AMPERE CURRENT RATING; IMPACT RESISTANT; (2) 18 AWG CORD SIZE; HOMeselect[T] BRAND
Type	Main circuit breaker
unspsc code	39121101

Availability

Status	Inactive
--------	----------

Packaging

Carton	1
Weight Per each	22

Uses, Certifications, and Standards

Application	Power Distribution
Enclosure	NEMA 1
Mounting standard	Combination UL 67; UL 50