



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BR1632B200 16/32C 200A 1PH MB Loadcenter

Eaton Corp

| | |
|------------------|--|
| Catalog Number | BR1632B200 |
| Manufacturer | Eaton Corp |
| Description | BR Style 1-Inch Loadcenter, Main Circuit Breaker, No Feed-Thru Lugs, 200A, Single-Phase, 32-Pole, 32 Circuits, 16 Spaces, 120/240V, #2/0-300 Kcmil Cu/Al At 60°C or 75°C Wire, Nema 1 Enclosure, C4 Box Size |
| Weight per unit | 27.4 (lbs/each) |
| Product Category | Single Phase Main Breaker Load |

Features

| | |
|----------------------|--------------------------------------|
| amperage rating | 59120 |
| Box Size | HID Floodlight |
| cover | Cover included |
| Cover Type | Cover included |
| dimensions | 5.0000 IN X 13.0000 IN X 15.0000 IN |
| interrupt rating | 25 kAIC |
| main circuit breaker | BWH |
| Number of Circuits | 32 W |
| number of spaces | 16 OZ |
| Number of Wires | Three-wire |
| Phase | 1 PH |
| used with | Type BR 1-inch breakers |
| Voltage Rating | 120/240 VAC |
| Wire Size | #2/0-300 kcmil Cu/Al at 60°C or 75°C |

Material, Color, and Finish

| | |
|--------------------|----------|
| Bus Material | Aluminum |
| Enclosure Material | Metallic |

Dimensions and Weight

| | |
|------|----|
| Size | C4 |
|------|----|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|--|
| Description | 16/32C 200A 1PH MB LOADCENTER |
| extra long description | ETN BR1632B200 BR style 1-inch load |
| Long Description | BR style 1-inch loadcenter, main circuit breaker, no feed-thru lugs, 200A, single-phase, 32-pole, 32 circuits, 16 spaces, 120/240V, #2/0-300 kcmil Cu/Al at 60°C or 75°C wire, NEMA 1 enclosure, c4 box size |
| Product Type | BR Style 1-Inch Loadcenter |
| Special Features | No feed-thru lugs |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Eaton |
| GTIN | 00786676445351 |
| Manufacturers Part Number | BR1632B200 |
| UPC | 786676445351 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | LOADCENTERS & COVERS |
| igcc | PLUG, NON POLARIZED TYPE; THERMOPLASTIC MATERIAL; WHITE COLOR; 1-15P CONFIGURATION; UL 1706, CSA APPROVAL; 125 V VOLTAGE RATING; 15 AMPERE CURRENT RATING; IMPACT RESISTANT; (2) 18 AWG CORD SIZE; HOMeselect[T] BRAND |
| Type | Main circuit breaker |
| unspsc code | 39121101 |

Availability

| | |
|--------|----------|
| Status | Inactive |
|--------|----------|

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight Per each | 27.4 |

Uses, Certifications, and Standards

| | |
|-------------|--------------------|
| Application | Power Distribution |
| Enclosure | NEMA 1 |
| Mounting | Combination |
| standard | UL 67; UL 50 |