



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## BR2030 BR Duplex BRKR 1-20A/1-30A 1 Pole 120/240V 10K Non

*Eaton Corp*

Catalog Number	BR2030
Manufacturer	Eaton Corp
Description	Eaton BR Thermal Magnetic Circuit Breaker, Type BR 1-Inch Plug-On Circuit Breaker, C, 120V, BR, Common Breaker Trip, #14-4 Awg Cu/Al, Q28, BR, Type BR Loadcenters
Weight per unit	0.4000 (lbs/each)
Product Category	Duplex Standard Trip Plug-In

### Features

dimensions	3.0000 IN X 1.0000 IN X 3.0000 IN
interrupt rating	10
Poles	2
Voltage Rating	120 V

### Descriptions

Description	BR DUPLEX BRKR 1-20A/1-30A 1 POLE 120/240V 10K NON
extra long description	ETN BR2030 BR Duplex 1-20A/1-30A 1P
Features	Eaton's BR circuit breakers are used in indoor and outdoor BR loadcenters, spa panels, meter breakers and sub panels. They are designed for a wide range of applications such as high short-circuit interrupt, series rating combinations with upstream main breakers, thermal magnetic, AFCI, GFCI, equipment protection and dual function AF/GF.
Long Description	Eaton BR thermal magnetic circuit breaker, Type BR 1-Inch plug-on circuit breaker, c, 120V, BR, Common breaker trip, #14-4 AWG Cu/Al, Q28, BR, Type BR Loadcenters
Product Type	BR Duplex 1-20A/1-30A 1P 120/240V 10K

### Manufacturer Information

Brand	Eaton
GTIN	00786676006606
Manufacturers Part Number	BR2030
UPC	786676006606

### Taxonomies, Classifications, and Categories

Category Description	Specialty Breakers (Quad, Dupl, Shunt Trip)
Type	Thermal magnetic circuit breakers

### Packaging

Carton	1
Weight Per each	0.4



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Marine Vessels and Equipment - Marine Vessels and Equipment -  
OtherOtherGeneration - Renewable Energy - Alternative  
EnergyGeneration - Conventional Energy - Conventional  
EnergyDatacenters - IT Space: CI and Hyper Converged

standard

UL 489, Federal Specifications Classification W-C375