

# Specifications



## Eaton BR20W

Eaton commercial specification grade duplex receptacle, #14-10 AWG, 20A, Commercial, Flush, 125V, Back and side, White, Brass, High-impact nylon, PVC, 5-20R, Duplex, Screw, PVC, Core pack

### General specifications

|                             |                                                              |
|-----------------------------|--------------------------------------------------------------|
| <b>PRODUCT NAME</b>         | Eaton commercial specification grade duplex receptacle       |
| <b>CATALOG NUMBER</b>       | BR20W                                                        |
| <b>UPC</b>                  | 032664750724                                                 |
| <b>PRODUCT LENGTH/DEPTH</b> | 1.3 in                                                       |
| <b>PRODUCT HEIGHT</b>       | 4.2 in                                                       |
| <b>PRODUCT WIDTH</b>        | 0.88 in                                                      |
| <b>PRODUCT WEIGHT</b>       | 0.21 lb                                                      |
| <b>CERTIFICATIONS</b>       | UL<br>NOM<br>Federal Specification<br>Classification 6233 01 |
| <b>PRODUCT TYPE</b>         | Commercial specification grade                               |

## Product specifications

|                     |                                                            |
|---------------------|------------------------------------------------------------|
| DEVICE TYPE         | Receptacle                                                 |
| TYPE                | Duplex receptacle                                          |
| AMPERAGE RATING     | 20A                                                        |
| VOLTAGE RATING      | 125V                                                       |
| CONTACT MATERIAL    | Brass                                                      |
| FEATURES            | Auto-grounding                                             |
| APPLICATION         | Commercial                                                 |
| DEVICE GRADE        | Commercial                                                 |
| WIRING METHOD       | Back and side                                              |
| NUMBER OF WIRES     | 3                                                          |
| MOUNTING METHOD     | Flush                                                      |
| NUMBER OF POLES     | Two-pole                                                   |
| STYLE TYPE          | Standard                                                   |
| MATERIAL            | PVC                                                        |
| PACKAGING TYPE      | Core pack                                                  |
| COLOR               | White                                                      |
| CONNECTION TYPE     | Screw                                                      |
| ALLOWABLE WIRE SIZE | Side or Back Wiring :#10-12 Copper or Copper Clad Aluminum |
| NEMA CONFIGURATION  | 5-20R                                                      |
| TORQUE RATING       | 14 lbf-inch                                                |
| DESIGN TYPE         | Straight blade                                             |
| FACE/BODY MATERIAL  | PVC<br>High-impact nylon                                   |
| RECEPTACLE TYPE     | Duplex                                                     |

## Resources

|                               |                                                                               |
|-------------------------------|-------------------------------------------------------------------------------|
| MULTIMEDIA                    | <a href="#">Residential straight blade receptacles</a>                        |
| SPECIFICATIONS AND DATASHEETS | <a href="#">Eaton Specification Sheet - BR20W</a>                             |
|                               | <a href="#">Commercial grade straight blade duplex receptacles spec sheet</a> |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

