



## BT1MCO 4" Nyln CBL Tie SS Barb Min Cross Sec BLCK

*Panduit Corporation*

Catalog Number

BT1MCO

Manufacturer

Panduit Corporation

Description

The BT1M-C0 Dome-Top® Barb Ty, Features A Unique Patented Design With Its Round Smooth Edges. Paired With The Stainless-Steel Locking Barb, These Cable Ties Provide Consistent Performance, Reliability and Infinite Adjustability Through The Entire Bundle Range. Miniature Cross Section, 4.0" (102MM) Length. Appropriate For Indoor/Outdoor Use, Made Of Weather Resistant Nylon 6.6 With High Resistance to Ultraviolet Light, Are Black In Color and Come In Packages Of 100.

Weight per unit

1.0 (lbs/each)

Product Category

Cable Ties & Wraps

### Features

media

Yes

Tensile Strength

18

### Dimensions and Weight

Length

4

Thickness

0.04

### Descriptions

Description

4" NYLN CBL TIE SS BARB MIN CROSS SEC BLCK

extra long description

PAN BT1M-C0 Dome-Top® BT1M-C0 Barb

Long Description

The BT1M-C0 Dome-Top® barb ty, features a unique patented design with its round smooth edges. Paired with the stainless-steel locking barb, these cable ties provide consistent performance, reliability and infinite adjustability through the entire bundle range. Miniature cross section, 4.0" (102mm) length. Appropriate for Indoor/Outdoor use, made of Weather Resistant Nylon 6.6 with high resistance to ultraviolet light, are black in color and come in packages of 100.

Product Type

Dome-Top® BT1M-C0 Barb Tie, Black, Uv PA6.6, 4" L, 18LB, PK10

Special Features

Indoor/Outdoor



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2805 Poplar  
75402-0000, TX Greenville  
Phone: 903-454-3354  
Fax: 903-454-8926

## Manufacturer Information

Brand	PANDUIT
GTIN	00074983413034
Manufacturers Part Number	BT1M-C0
UPC	074983413034

## Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	Cable Tie

## Availability

minimum qty	100
-------------	-----

## Packaging

Carton	100
Package	1000
Weight Per each	1

## Uses, Certifications, and Standards

standard	UL 62275 (File E56854), CSA-C22.2 No. 62275, 11130200, NRC 10CFR50, QPL-AS23190, CSA Certified, RoHS Compliant
----------	--