



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BR4040N200 40/40C 200A 1PH Convertible Loadcenter

Eaton Corp

| | |
|------------------|---|
| Catalog Number | BR4040N200 |
| Manufacturer | Eaton Corp |
| Description | BR Style 1-Inch Loadcenter, Convertible Main, Ground Bar, 200A, Single-Phase, 40-Pole, 40 Circuits, 40 Spaces, 120/240V, Depends Upon Main Breaker Kit or Main Lug Kit Chosen., Nema 1 Enclosure, L1 Box Size |
| Weight per unit | 35.9 (lbs/each) |
| Product Category | Single Phase Convertible Load |

Features

| | |
|----------------------|---|
| amperage rating | 59120 |
| Box Size | PCA18-1 |
| cover | Cover included |
| Cover Type | Cover included |
| dimensions | 5.5000 IN X 14.3100 IN X 41.0000 IN |
| interrupt rating | 10 kAIC |
| main circuit breaker | Environmental Conditions Wet Location; Includes Ground Screw; Shape Round |
| Number of Circuits | 40 DEG C |
| number of spaces | 40 W |
| Number of Wires | Three-wire |
| Phase | 1 PH |
| used with | Type BR 1-inch breakers |
| Voltage Rating | 120/240 VAC |
| Wire Size | Determined by circuit breaker installed |

Material, Color, and Finish

| | |
|--------------------|----------|
| Bus Material | Aluminum |
| Enclosure Material | Metallic |

Dimensions and Weight

| | |
|------|----|
| Size | L1 |
|------|----|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | 40/40C 200A 1PH CONVERTIBLE LOADCENTER |
| extra long description | ETN BR4040N200 BR style 1-inch load |
| Long Description | BR style 1-inch loadcenter, convertible main, ground bar, 200A, single-phase, 40-pole, 40 circuits, 40 spaces, 120/240V, depends upon main breaker kit or main lug kit chosen., NEMA 1 enclosure, I1 box size |
| Product Type | BR Style 1-Inch Loadcenter |
| Special Features | Ground bar |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Eaton |
| GTIN | 00786676449007 |
| Manufacturers Part Number | BR4040N200 |
| UPC | 786676449007 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | LOADCENTERS & COVERS |
| igcc | PLUG, NON POLARIZED TYPE; THERMOPLASTIC MATERIAL; WHITE COLOR; 1-15P CONFIGURATION; UL 1706, CSA APPROVAL; 125 V VOLTAGE RATING; 15 AMPERE CURRENT RATING; IMPACT RESISTANT; (2) 18 AWG CORD SIZE; HOMeselect[T] BRAND |
| Type | CONVERTIBLE MAIN |
| unspsc code | 39121101 |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight Per each | 35.9 |

Uses, Certifications, and Standards

| | |
|-------------|--------------------|
| Application | Power Distribution |
| Enclosure | NEMA 1 |
| Mounting | Combination |
| standard | UL 67;UL 50 |