



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## BRCAF120CS Eaton BR AfcI Circuit Bre Eaton Corp

Catalog Number	BRCAF120CS
Manufacturer	Eaton Corp
Description	Eaton BR AfcI Circuit Breaker, AfcI Circuit Breaker, Clamshell Pack, 20 A, 10 Kaic, Single-Pole, 120 V, BRC, Pigtail, #14-4 Awg Cu/Al, Q30, Type BR Loadcenters
Weight per unit	0.4500 (lbs/each)
Product Category	In Circuit Breakers

### Features

connection	Pigtail
dimensions	6.0000 IN X 3.5000 IN X 1.2500 IN
interrupt rating	10
Poles	1
Voltage Rating	120 V

### Descriptions

Description	EATON BR AFCI CIRCUIT BRE
extra long description	ETN BRCAF120CS BR COMBINATION AFCI,
Features	Eaton's BR circuit breakers are used in indoor and outdoor BR loadcenters, spa panels, meter breakers and sub panels. They are designed for a wide range of applications such as high short-circuit interrupt, series rating combinations with upstream main breakers, thermal magnetic, AFCI, GFCI, equipment protection and dual function AF/GF.
Long Description	Eaton BR AFCI circuit breaker, AFCI Circuit breaker, Clamshell pack, 20 A, 10 kAIC, Single-pole, 120 V, BRC, Pigtail, #14-4 AWG Cu/Al, Q30, Type BR Loadcenters
Product Type	BR Combination AfcI, 1P, 20A, 10KAIC,
Special Features	Clamshell pack

### Manufacturer Information

Brand	Eaton
GTIN	00786685514376
Manufacturers Part Number	BRCAF120CS
UPC	786685514376

### Taxonomies, Classifications, and Categories

Category Description	Loadcenter Plug In Breakers and Accessories
Type	AFCI circuit breakers

### Packaging

Carton	1
Weight Per each	0.45



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Generation - Conventional Energy - Conventional  
EnergyOtherMarine Vessels and Equipment - Marine Vessels and  
Equipment - OtherGeneration - Renewable Energy - Alternative  
EnergyDatacenters - IT Space: CI and Hyper Converged

standard

UL 1699,Federal Specifications Classification W-C375