



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## BRH240 Type BR BRKR 40A/2 Pole Com. Trip 120/240V 22K

Eaton Corp

Catalog Number	BRH240
Manufacturer	Eaton Corp
Description	Eaton BR Thermal Magnetic Circuit Breaker, Type BR 1-Inch Plug-On Circuit Breaker, 40 A, 22 Kaic, Two-Pole, 120/240V, BRH, Common Breaker Trip, #14-4 Awg Cu/Al, Q28, BRH, Type BR Loadcenters
Weight per unit	0.6000 (lbs/each)
Product Category	2 Pole Standard Trip Plug-In

### Features

dimensions	3.0000 IN X 2.0000 IN X 3.0000 IN
interrupt rating	22 kAIC
Poles	2
Trip Type	Common breaker trip
Voltage Rating	120/240 V

### Descriptions

Description	TYPE BR BRKR 40A/2 POLE COM. TRIP 120/240V 22K
extra long description	ETN BRH240 BR 40A/2 Pole Com. Trip
Features	Eaton's BR circuit breakers are used in indoor and outdoor BR loadcenters, spa panels, meter breakers and sub panels. They are designed for a wide range of applications such as high short-circuit interrupt, series rating combinations with upstream main breakers, thermal magnetic, AFCI, GFCI, equipment protection and dual function AF/GF.
Long Description	Eaton BR thermal magnetic circuit breaker, Type BR 1-Inch plug-on circuit breaker, 40 A, 22 kAIC, Two-pole, 120/240V, BRH, Common breaker trip, #14-4 AWG Cu/Al, Q28, BRH, Type BR Loadcenters
Product Type	BR 40A/2 Pole Com. Trip 120/240V 22K

### Manufacturer Information

Brand	Eaton
GTIN	00786676373654
Manufacturers Part Number	BRH240
UPC	786676373654

### Taxonomies, Classifications, and Categories

Category Description	Loadcenter Plug In Breakers and Accessories
Type	Thermal magnetic circuit breakers



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	0.6

## Uses, Certifications, and Standards

Application	OtherGeneration - Conventional Energy - Conventional EnergyDatacenters - IT Space: CI and Hyper ConvergedMarine Vessels and Equipment - Marine Vessels and Equipment - OtherGeneration - Renewable Energy - Alternative Energy
standard	UL 490,Federal Specifications Classification W-C376