

# Eaton BRP115AF

Catalog Number: BRP115AF

Eaton BR AFCI circuit breaker, AFCI Combination circuit breaker, UL only, 15 A, 10 kAIC, Single-pole, 120 V, BR, Plug-on, #14-8 AWG Cu/Al, Type BR Loadcenters, Plug-on neutral



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR AFCI circuit breaker	BRP115AF
<b>UPC</b>	<b>Product Length/Depth</b>
786689041014	2.56 in
<b>Product Height</b>	<b>Product Width</b>
1.1 in	1 in
<b>Product Weight</b>	<b>Certifications</b>
0.38 lb	UL Listed

## Product specifications

### Used with

Type BR Loadcenters

### Type

AFCI Combination circuit breaker

### Special features

UL only

### Amperage Rating

15 A

### Voltage rating

120 V

### Neutral

Plug-on neutral

### Interrupt rating

10 kAIC

### Main circuit breaker

BR

### Connection

Plug-on

### Wire size

#14-8 AWG Cu/Al

### Number of poles

Single-pole

## Resources

### Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton BRP115AF

Catalog Number: BRP115AF

Eaton BR AFCI circuit breaker, AFCI Combination circuit breaker, UL only, 15 A, 10 kAIC, Single-pole, 120 V, BR, Plug-on, #14-8 AWG Cu/Al, Type BR Loadcenters, Plug-on neutral



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR AFCI circuit breaker	BRP115AF
<b>UPC</b>	<b>Product Length/Depth</b>
786689041014	2.56 in
<b>Product Height</b>	<b>Product Width</b>
1.1 in	1 in
<b>Product Weight</b>	<b>Certifications</b>
0.38 lb	UL Listed

## Product specifications

### Used with

Type BR Loadcenters

### Type

AFCI Combination circuit breaker

### Special features

UL only

### Amperage Rating

15 A

### Voltage rating

120 V

### Neutral

Plug-on neutral

### Interrupt rating

10 kAIC

### Main circuit breaker

BR

### Connection

Plug-on

### Wire size

#14-8 AWG Cu/Al

### Number of poles

Single-pole

## Resources

### Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)