



BRP40B200 BR Pon Loadcntr 200A 25KAIC MCB 40/80 Cir. Al Bus

Eaton Corp

Catalog Number	BRP40B200
Manufacturer	Eaton Corp
Description	Eaton BR Main Breaker Loadcenter, Ground Bar, Includes BREQS125 Hold-Down Screw, Plug-On Neutral Main Circuit Breaker Loadcenter, 200 A, X8, Aluminum, Cover Included, Nema 1, Metallic, 25 Kaic, CSR, 80 Circuits, Single Pole, 40 Spaces
Weight per unit	36.0 (lbs/each)
Product Category	Single Phase Main Breaker Load

Features

amperage rating	200
Cover Type	Cover included
interrupt rating	25
number of spaces	40
Phase	1
Voltage Rating	120/240 V
Wattage	Single-pole

Dimensions and Weight

Depth	39
Height	3.88
Size	X8
Width	15.5

Descriptions

Description	BR PON LOADCNTR 200A 25KAIC MCB 40/80 CIR. AL BUS
extra long description	ETN BRP40B200 BR PON LC 200A 25KAIC
Features	Specially designed for easy installation, Eaton's BR 1-inch load centers house the branch circuit breakers and the wiring required to distribute power to individual circuits. They serve as main breaker for service entrances or as main lug when adding circuits to existing service. The main breaker protects the entire panel and can be used as a service disconnect. The branch breakers protect the wires leading to individual electrical loads such as fixtures and outlets.
Long Description	Eaton BR main breaker loadcenter, Ground bar, includes BREQS125 hold-down screw, Plug-on neutral main circuit breaker loadcenter, 200 A, X8, Aluminum, Cover included, NEMA 1, Metallic, 25 kAIC, CSR, 80 circuits, Single pole, 40 spaces
Product Type	BR Pon LC 200A 25KAIC MCB 40 SPC Al Bus
Special Features	Ground bar, includes BREQS125 hold-down screw



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3507 N Van Buren Bypass
73701-0000, OK Enid
Phone: 580-701-6818
Fax: 580-234-5655

Manufacturer Information

Brand	Eaton
GTIN	00786689044053
Manufacturers Part Number	BRP40B200
UPC	786689044053

Taxonomies, Classifications, and Categories

Category Description	LOADCENTERS & COVERS
Type	Main breaker loadcenter

Packaging

Carton	1
Weight Per each	36

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & EOEM - Electrical Assemblies, Panels and EOEMs
Mounting	Combination Mount
standard	UL 50,UL 67