



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



C25DND330C Open N-R 3P 30A DP Cont SCR/PP W/QC Term 480VAC CO *Eaton Corp*

Catalog Number	C25DND330C
Manufacturer	Eaton Corp
Description	Eaton Definite Purpose Contactor, Quick, 30A, 440-480 Vac, 50/60 HZ, Open With Metal Mounting Plate, 15-50A, Two- and Three-Pole, 30A, Contactor, Three-Pole, 40A, Screw/Pressure Plate and Quick Connect Terminals (Side-By-Side), Non-Reversing
Weight per unit	1.2 (lbs/each)
Product Category	Definite Purpose Contactors

Features

Enclosure Type	Open with metal mounting plate
induct amp/res amp rating	30/40
Voltage Rating	480

Dimensions and Weight

Depth	3.35
Height	3.6
Width	2.4

Descriptions

Description	OPEN N-R 3P 30A DP CONT SCR/PP W/QC TERM 480VAC CO
extra long description	ETN C25DND330C OP N-R 3P 30ADPCNT S
Features	Definite purpose contactors and starters are electrically operated switching devices specifically designed for the heating, ventilation, air conditioning and refrigeration (HVAC) industry.
Long Description	Eaton definite purpose contactor, Quick, 30A, 440-480 Vac, 50/60 Hz, Open with metal mounting plate, 15-50A, two- and three-pole, 30A, Contactor, Three-pole, 40A, Screw/pressure plate and quick connect terminals (side-by-side),Non-reversing
Product Type	Op N-R 3P 30ADPCNT SCR/PP W/QC480VCL

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782116308859
Manufacturers Part Number	C25DND330C
UPC	782116308859

Taxonomies, Classifications, and Categories

Category Description	DP CONTACTORS
Type	Definite purpose contactor



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	1.19

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
standard	CSA Certified,UL Recognized,RoHS Compliant