



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BUB7SA 2-1/2" Alu Bub MGL Conduit Body

Crouse-Hinds

Catalog Number	BUB7SA
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Condulet B Mogul Conduit Body, Copper-Free Aluminum, Ub Shape, 2-1/2"
Weight per unit	5.4 (lbs/each)
Product Category	Alum

Features

dimensions	17.7500 IN X 4.2500 IN X 4.8100 IN
------------	------------------------------------

Dimensions and Weight

Height	5-5/8
Hub Size	3 in
Length	17-7/8

Descriptions

Description	2-1/2" ALU BUB MGL CONDUIT BODY
extra long description	CRS-H BUB7 SA 2 1/2 NPT AL UB MOGUL
Features	Crouse-Hinds series mogul bodies are installed in conduit systems to act as pull outlets for conductors that are stiff due to large size or type of insulation. Mogul bodies provide longer openings needed when pulling large conductors and prevent sharp bends and kinks during installation. Mogul conduit bodies are manufactured in trade sizes 1/2" to 6" and are available in Feraloy iron alloy and copper-free aluminum. Our iron alloy bodies are available with a hot dip galvanized finish for added corrosion
Long Description	Eaton Crouse-Hinds series Condulet B mogul conduit body, Copper-free aluminum, UB shape, 2-1/2"
Product Type	2 1/2 NPT Al Ub Mogul

Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00782274127231
Manufacturers Part Number	BUB7 SA
UPC	782274127231

Taxonomies, Classifications, and Categories

Category Description	Form 9 condulets, covers & gaskets
Type	Mogul conduit body

Packaging

Carton	1
Weight Per each	5.4499



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
standard	UL 514B, CSA C22.2, FEDERAL SPECIFICATION W-C-586D