



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## BUB9 3-1/2" Bub Conduit Body

*Crouse-Hinds*

Catalog Number	BUB9
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Condulet B Mogul Conduit Body, Feraloy Iron Alloy, Ub Shape, 3-1/2"
Weight per unit	26.9 (lbs/each)
Product Category	Bodies & Covers

### Features

dimensions	23.3800 IN X 5.2500 IN X 6.3800 IN
------------	------------------------------------

### Dimensions and Weight

Height	6-3/8
Hub Size	3-1/2 in
Length	23-3/8
Width	5-1/4

### Descriptions

Description	3-1/2" BUB CONDUIT BODY
extra long description	CRS-H BUB9 3 1/2 NPT IRON UB MOGUL
Features	Crouse-Hinds series mogul bodies are installed in conduit systems to act as pull outlets for conductors that are stiff due to large size or type of insulation. Mogul bodies provide longer openings needed when pulling large conductors and prevent sharp bends and kinks during installation. Mogul conduit bodies are manufactured in trade sizes 1/2" to 6" and are available in Feraloy iron alloy and copper-free aluminum. Our iron alloy bodies are available with a hot dip galvanized finish for added corrosion
Long Description	Eaton Crouse-Hinds series Condulet B mogul conduit body, Feraloy iron alloy, UB shape, 3-1/2"
Product Type	3 1/2 NPT Iron Ub Mogul

### Manufacturer Information

Brand	Eaton
GTIN	00782274108902
Manufacturers Part Number	BUB9
UPC	782274108902

### Taxonomies, Classifications, and Categories

Category Description	FORM 7, 8, CONDULETS, COVERS, & GASKETS
Type	Mogul conduit body



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	26.9

## Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
standard	UL 514B, CSA C22.2, FEDERAL SPECIFICATION W-C-586D