



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



C1FC50LE Potted 1PH 500VA 240X480-120/240

Hammond Power Solutions

| | |
|------------------|--|
| Catalog Number | C1FC50LE |
| Manufacturer | Hammond Power Solutions |
| Description | 600V Class Commercial Potted Single Phase Distribution Transformer, 240X480 PV, 120/240 SV, 0.50 Kva |
| Weight per unit | 16.0 (lbs/each) |
| Product Category | Encapsulated Industrial Contro |

Features

| | |
|----------------|--------------|
| Input Voltage | 240X480 |
| Output Voltage | 120/240 |
| Phase | Single Phase |
| Wattage | 0.5 |

Dimensions and Weight

| | |
|--------|------|
| Height | 7.25 |
| Length | 5.75 |
| Width | 4.5 |

Descriptions

| | |
|------------------------|--|
| Description | POTTED 1PH 500VA 240X480-120/240 |
| extra long description | HMND C1FC50LE POTTED 1PH 500VA 240X |
| Long Description | 600V Class Commercial Potted Single Phase Distribution Transformer, 240x480 PV, 120/240 SV, 0.50 kVA |
| Product Type | Pott 1PH 240X480 PV 120/240 SV 0.50kva |
| Special Features | Innovative potted design provides single screw access on a hinged cover to the wiring compartment for commercial indoor and outdoor applications |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | HPS Fortress™ |
| GTIN | 00803423090692 |
| Manufacturers Part Number | C1FC50LE |
| UPC | 803423090692 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | BUCK & BOOST TRANSFORMERS |
| Type | Transformer > Distribution > Potted > Commercial > Single Phase |

Packaging

| | |
|-----------------|----|
| Carton | 1 |
| Weight Per each | 16 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------------|---|
| Application | Shopping centers, schools, sports complexes, commercial, lighting, wastewater and light industrial loads. |
| Enclosure | NQ1-N3R - Indoor or Outdoor |
| Frequency Rating | 60 |
| Mounting standard | WALL MOUNT CSA, UL |